

DESCRIPTION

The 164 series is a decorative wall sconce family with rectilinear form. This product is a square shape shade, with a variety of options to highlight elegant spatial forms. The integral LED light engine is available in 2700K, 3000K, 3500K, and 4000K color temperatures that evenly illuminates the shade and the bottom lens, and 83+ CRI. Shaper's Fabrique collection its known for is high quality hand tucked fabrics. Heavy gauged steel frame, laminated styrene backing, and minimum internal structure. Shades come in three sizes, eleven standard fabrics, and two translucent organza fabrics, allowing the designer to select a look for any space.

SPECIFICATION FEATURES

Construction

Aluminum housing, cold rolled steel cover and bracket extensions with LED boards attached. Optional matte white acrylic top cover available (TC).

164-12

Width is 12", height is 12", depth is 4" and ADA compliant.

Note: Consult factory for non standard lengths under 18" and over 96".

Painted Finishes

(canopy, stem, and finial)
ALP - Aluminum Paint
BM - Bronze Metallic
DP - Dark Platinum
GRM - Graphite Metallic
MB - Matte Black
CC - Custom Color
Consult factory for custom color.

Shades

Aluminum wire frame painted white. Material backed on to heavy translucent white styrene. All shades have "Hand-Tucked Rolled Edges" except for Vinyl.

Fabric Shade Selections

SIW - Silk White
SIY - Silk Ivory
SWH - Shantung White
SEG - Shantung Eggshell
SBG - Shantung Beige
GBB - Glynn Brussels Beige
LOLA - Lola Sand
NGS - Silk Glow
LCK - Linen Chopstick
LAT - Linen Alabaster
VLW - Verona Linen White

Vinyl Coated Fabric

ABR - Alabaster Vinyl*
NFX - Natural Flax*
GHY - Golden Honey*

Printed Woods

PVDB - Varigated Bamboo
PMA - Maple
PCH - Cherry
PWA - Walnut

Note: For humid environments, such as showers or open lobbies, Vinyl Coated Fabrics are recommended.

Electrical

Standard driver is electronic universal voltage (120-277V, 50/60 Hz), greater than 0.9 power factor, less than 20% harmonic distortion, and ambient temperatures of 25°C (77°F).

Control

Standard driver is 0-10V with 10% dimming.

Compliance

Components are UL recognized and luminaires are cUL listed for 25° ambient environments. Fixtures are rated for damp location listing. Made in North America. Cooper Lighting Solutions certifies that its products satisfy the requirements of ARRA Section 1605 of the American Recovery Reinvestment Act. All LED components are RoHS compliant and drivers conform to appropriate FCC regulations. Sconce products meet ADA regulations.

Life and Warranty

Standard five-year warranty on all parts.



164-W Series LED

Surface
Decorative LED Wall Sconce

cULus - 1598
Damp Location
LM79/LM80 Compliant

Length 12"

- Delivered Lumens (@3500K) 2458
- Wattage: 28W
- CRI: 80
- CCT: 2700K, 3000K, 3500K, 4000K

ORDERING INFORMATION (Select FIXTURE NUMBER and SHADE NUMBER to complete specification)

Fixture Number: 164-12-W-L2/827-UNV

Series ¹	Size	Mounting Type	LED Lamp	LED Voltage	Options ²
164 = Square Wall Sconce	12"	Wall = Wall	L2/827 L2/830 L2/835 L2/840	UNV (120-277)	TC = Matte White Acrylic Top Cover RBP = Remote Battery Pack

Notes: ¹ Fabric Kit is not included. Please specify Fabric Kit (below) to complete specification. ² 5" Max Mounting Distance.

Shade Number: 164-12-SHD-SIW

Series	Size	Shade	Finish			
164 = Square Wall Shade	12"	SHD = Shade Fabric	Fabric: SIW = Silk White SIY = Silk Ivory SWH = Shantung White SEG = Shantung Eggshell SBG = Shantung Beige GBB = Glynn Brussels Beige	LOLA = Lola Sand NGS = Silk Glow LCK = Linen Chopstick LAT = Linen Alabaster VLW = Verona Linen White	Vinyl: ABR = Alabaster Vinyl NFX = Natural Flax GHY = Golden Honey	Printed Woods: PVDB = Varigated Bamboo PMA = Maple PCH = Cherry PWA = Walnut