

Project: _____


Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Ordering Guide

Example: LLL 6 AC

Product Code	LLL	Copper Steplyte
Options	6 12 24	6" Length 12" Length 24" Length
Finish	AC	Hand-Crafted Copper

Specifications

HOUSING:

Seamless solid copper extrusions with solid copper ends. Tool-less lamp access.

FINISH:

Natural Copper is bright polished, untreated copper. Color will age naturally to a fine dark copper patina.

OPTICAL ASSEMBLY:

Reflector is Stainless Steel.

LAMPING:

10W wedge base T3 1/4 (xenon) lamp is included with fixture. Xenon lamp life is approximately 10,000 hours. Lower wattage lamps are acceptable. Lamp does not need to be protected and can be directly handled.

ELECTRICAL ASSEMBLY:

Wedge base socket type (T3-1/4 or T5). Socket is hinged for easy relamping. 12 volt fixture is pre-wired with 6-ft. pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

INSTALLATION & MOUNTING:

Two (2) Stainless #8 wood screws (supplied) via key slots.

WARRANTY:

Ten-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Height :

1" (25mm)

Width:

1" (25mm)

