

PHILIPS

Wall light

myGarden

Flagstone

inox

LED



17209/47/16



Light up your outdoor life

Minimalistic in design yet solid in function. This Philips wall light in stainless steel casts powerful warm white LED light. Add a unique glow to your wall with bi-directional light effects.

Sustainable light solutions

- Extremely long operating life
- Energy saving
- Philips offers 5 year warranty on the LED module and driver

Designed for outdoors

- Modern outdoor lighting
- Choose for outdoor wall lights
- High quality stainless steel and real glass

Advanced light for outdoors

- High power LED
- Powerful light
- Philips offers 5 year warranty on the LED module and driver

Special characteristics

- Bi-directional light effect
- Easy to set up for every application
- Weather proof

Highlights

Extremely long operating life



A light source you can trust. Philips LED lights offer an extremely long-life of at least 20.000 hours (which equals 20 years on basis of an average use of 3 hours / day with an amount of at least of 13.000 on/off switching cycles). With the Philips LED lights you won't have to worry about maintenance or lamp replacement while having the perfect light ambience in your home.

Energy saving



This Philips light conserves energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

5 year warranty on LED system



On top of the standard 2 year warranty for this lamp, Philips offers 5 year warranty on the LED system, meaning the LED module and the driver in this lamp.

Modern outdoor lighting

Impressive, bold and minimalist outdoor lighting by Philips. Philips outdoor is elegant modern style is the perfect way to grace gardens, pathways and outdoor spaces with light.

Choose for outdoor wall lights

Make the most of your outdoor space with this wall light, perfect to mount close to your front door or on your terrace walls.

High quality material

This Philips lamp is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high quality stainless steel and real glass.

High power LED



Philips outdoor lighting uses the latest state-of-the-art LED technology. It offers strong light output and high light quality and long lifetime.

Powerful light

This outdoor lamp provides powerful warm white light. A bright pool of light to light up your garden or terrace.

5 year warranty on LED system



On top of the standard 2 year warranty for this lamp, Philips offers 5 year warranty on the LED system, meaning the LED module and the driver in this lamp.

Bi-directional light effect



Bi-directional light effect for general garden illumination.

Easy to set up

This lamp and the fittings are designed for a straightforward installation with all useful things that you need to get up and running included in the box, like a Torx key and Torx screw. You'll find clear guidance about where you can install the product and relevant information about water-resistant IP ratings.

Weather proof

This Philips outdoor lamp is especially designed for humid outdoor

environments and has undergone rigorous tests to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This lamp is designed with IP44: it is protected against splashing water, this product is most common and ideal for general outdoor use.

Specifications

Design and finishing

- Color: Inox
- Material: Aluminium
- Housing Color: Inox

Durability

- Nominal lifetime: 25,000

Extra feature/accessory incl.

- 5 years warranty on the LED module: Yes
- Bi-directional light beams: Yes
- Fully weatherproof: Yes
- LED integrated: Yes

Garden area

- Garden area: Backyard, Frontyard

Miscellaneous

- Especially designed for: Garden & Patio
- Style: Modern
- Type: Wall Lights
- EyeComfort: Yes

Power

- Input Voltage: SELV

Product dimensions and weight

- Net weight: 0.767 kg
- Height: 11.8 cm
- Length: 13.6 cm
- Width: 8.8 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Light source equivalent to traditional bulb of: 12
- Total lumen output fixture: 300 lm
- Bulb technology: LED
- Light color: warm white
- Mains power: 50-60 Hz
- Energy class included light source: Built in LED
- Wattage bulb included: 1 W
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class I - Earthed
- Light source replaceable: No
- Ingress protection code: IP44 | Wire-protected, splash-proof
- Number of light sources: 1
- Protection class IEC: Safety class I



Issue date: 2025-08-30
Version: 0.370

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com