

PHILIPS

Star Ceiling/Wall Spotlight

Ceiling/Wall Spotlights

2700K

White

Dimmable

56240/31/16



Accent your home with light

This Philips myLiving Star LED wall spot speaks of timeless elegance with its chrome leg and powdered white paint body. With latest LED technology, this energy saving spot provides plenty of warm white light to brighten your room in style.

Sustainable light solutions

- Energy saving
- High quality LED light
- Warm white light
- Philips offers 5 year warranty on the LED module and driver
- Long operating life up to 30 years

Special characteristics

- Adjustable spot head

Highlights

Energy saving



This Philips energy saving lamp conserves energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

High quality LED light



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

Warm white light



Light can have different color temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more cosy light, while those with a higher Kelvin value produce a cool, more energising light. This Philips lamp offers warm white light for a cosy atmosphere.

5 year warranty on LED system



On top of the standard 2 year warranty for this lamp, Philips offers 5 year warranty on the LED system, meaning the LED module and the driver in this lamp.

Long operating (30 yrs)



A light source you can trust. The integrated LEDs, used in this Philips LED lamp, will last up to 30.000 hours (which equals 30 years on basis of an average use of 3 hours / day with an amount of at least of 13.000 on/off switching cycles). It feels so comfortable to think that you won't have to worry about maintenance or light bulb replacement while having the perfect light ambiance in your home.

Adjustable spot head



Direct the light where you want it most by simply adjusting, rotating or tilting the spot head of the lamp.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Metal

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 30,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Adjustable – rise and fall
- Defined light beams: Yes
- LED integrated: Yes

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Luminous Efficacy (rated) (Nom): 111 lm/W

Miscellaneous

- Especially designed for: Bedroom, Living Room, Kitchen, Office, Hall
- Style: Contemporary
- Type: Ceiling/Wall Spotlights
- EyeComfort: Yes
- Extra Features: Dimmable

Product dimensions and weight

- Net weight: 0.280 kg
- Overall height: 82 mm
- Overall length: 118 mm
- Overall width: 60 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Total lumen output fixture: 500
- Bulb technology: LED
- Light color: 2700
- Mains power: AC 220–240
- Fixture dimmable: Yes
- Energy class included light source: F
- Wattage bulb included: 6.5
- IP code: IP20 | Finger-protected
- Class of protection: Class I – Earthed
- Light source replaceable: No
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC – product: 8718291444848
- Net weight: 0.28 kg
- Gross weight: 0.35 kg
- Height: 14.3 cm
- Length: 7.3 cm
- Width: 9.3 cm



Issue date: 2025-08-02
Version: 0.1580

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com