

PHILIPS

Spot 50W PAR16
GU10

LED

2700K

300lm

10000h

8718699659288



Durable LED accent lighting with a focused bright beam

Philips LED spots provide a focused bright beam, an exceptionally long life, and significant energy savings. This spot is the perfect long-lasting replacement for 50W spots with a GU10 cap.

Choose for a sustainable solution

- Safe for any room and convenient to recycle

Create the right light for your home

- Perfect for accent lighting

Highlights

No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

Perfect for accent lighting



Modern lighting with a familiar wide angle light output (36 degrees), this LED spot is suitable for both accent lighting and general purpose lighting. It can be used in recessed cans and track light fixtures, and is ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Dimmable: No

Bulb dimensions

- Height: 5.4 cm
- Width: 5 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 10,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 36 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Nominal luminous flux: 300 lm
- Warm-up time to 60% light: instant full light

Miscellaneous

- EyeComfort: No

Other characteristics

- Efficacy: 106 lm/W

Packaging information

- EAN: 8718699659288
- EOC: 871869965928800
- Product title: Essential LED 3.2-50W GU10 827 36D1PF/10

Power consumption

- Power factor: 0.4
- Voltage: 220-230 V
- Wattage equivalent: 50 W
- Power Consumption: 3.2 W

Product dimensions and weight

- Length: 5.4 cm

Rated values

- Rated peak intensity: 600 cd

Technical specifications

- Frequency: 50 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699659288
- Net weight: 0.03 kg
- Gross weight: 0.05 kg
- Height: 8.9 cm
- Length: 5.1 cm
- Width: 5.1 cm



Issue date: 2025-06-14
Version: 0.91

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com