

PHILIPS

Downlight

Recessed Lights

6500K

White

8718699748791



Comfortable LED light that's easy on your eyes

With its robust design and optimal performance, Philips LED Performance downlight is the perfect luminaire that brings quality and brightness to any home spaces. Comfortable light that's easy on your eyes.

Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.
- Easy to install, safe to use

Durability

- Long life span up to 25,000 hours

Eye Care

- High quality of LED light brings out vivid colors

Highlights

Suitable for low ceilings Slim design

Easy to install, safe to use

The Philips LED retractable ceiling fan light has passed strict safety testing and includes drop-resistant screws and a sturdy design alongside other important safety features.

Long life span up to 25,000 hours

Philips LED technology extends your product's lifetime up to 25,000 hours

High quality LED light

Premium LED technology integrated into this Philips lamp. While instantly turned on, it enables an optimal light output and brings out vivid colors to assist kids' identification for color when drawing or reading

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Metal
- Housing Color: White
- Housing Material: Aluminum
- Optical cover finish: Frosted
- Optical cover material: Polystyrene

Durability

- Number of switch cycles: 12,500
- Ambient temperature range: -10 to +40 °C
- Nominal lifetime: 25,000 hour(s)

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Guarantee

- Warranty period: 1 years

Light characteristics

- Beam angle: 110 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Constant light output: No
- Correlated Color Temperature (Nom): 6500
- Initial chromaticity: (0.3130 , , 0.3370) 6 SDCM
- Light source replaceable: No
- Luminaire light beam spread: 110°
- Luminous Flux: 2,000 lm
- Optic material: Polystyrene
- Optic type: Beam angle 110°
- Reflector material: -
- Luminous Efficacy (rated) (Nom): 83.00 lm/W

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 335 mA
- Efficacy: 83 lm/W
- EU RoHS compliant: Yes

Power

- Input Voltage: 110 to 240
- Inrush current: 14.9 A
- Inrush time: 0.5 ms
- Power Factor (Fraction): 0.5

Power consumption

- Power Consumption: 24

Product dimensions and weight

- Net weight: 0.517 kg
- Cut out length: 28.2–28.5 cm
- Cut out width: 28.2–28.5 cm
- Height: 2 cm
- Length: 30 cm
- Recessed distance: 50 mm
- Width: 30 cm
- Overall diameter: 295 mm
- Overall height: 20 mm
- Overall length: 295 mm
- Overall width: 295 mm

Packaging dimensions and weight

- EAN/UPC – product: 8718699748791
- Net weight: 0.59 kg
- Gross weight: 0.68 kg
- Height: 34.2 cm
- Length: 3.1 cm
- Width: 30.3 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Diameter: 295 mm
- Total lumen output fixture: 2000
- Light color: 6500
- Mains power: 110–240
- Wattage bulb included: 24
- IP code: IP20
- Class of protection: Class II – Double Insulated
- Connection: Flying leads/wires
- Dimmable: No
- Driver/power unit/transformer: Power supply unit (On/Off)
- Driver included: Yes
- Fixation material: Steel
- Flammability mark: For mounting on normally flammable surfaces
- Glow-wire test: Temperature 650 °C, duration 30 s
- Ingress protection code: IP20 | Finger-protected
- Line Frequency: 50 or 60
- Mech. impact protection code: IK03 | 0.3 J
- Number of gear units: 1 unit
- Suitable for random switching: Not applicable
- Protection class IEC: Safety class II



Issue date: 2025-06-27
Version: 0.486

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com