

PHILIPS

Mauve Ceiling Light
6W

Ceiling Lights

4000K

White

Sensor



8719514431829



Motion sensing light for convenience and extra energy saving

Increase convenience while saving energy. Philips' motion sensing LED ceiling light is easily turned on and off by a sensor which means you can leave or enter rooms without fumbling for a switch. Its wide detection range and instant-on LED technology means your home's lighting is only even on when you need it

Easy to experience

- With its built-in automatic motion sensor, this luminaire switches on automatically when people walk by.
- Easy installation

Durability

- Energy saving

Highlights

Integrated motion sensor

Easy installation

No more hassle in installation. Just fix or hang securely on the wall or ceiling,

and plug in, now this luminaire is ready to light on.

Energy saving

Saves energy - which is good for your bills, and the environment.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Metal, Plastic

Durability

- Number of switch cycles: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Sensor

Other characteristics

- Lamp current: 45 mA
- Efficacy: 106 lm/W

Product dimensions and weight

- Net weight: 0.26 kg
- Height: 7.2 cm
- Length: 25 cm
- Width: 25 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 250 mm
- Total lumen output fixture: 640
- Light color: 4000
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: Yes
- IP code: IP20
- Class of protection: Class I

Packaging dimensions and weight

- EAN/UPC - product: 8719514431829
- Net weight: 0.26 kg
- Gross weight: 0.49 kg
- Height: 27.2 cm
- Length: 8.2 cm
- Width: 27.2 cm



Issue date: 2025-03-18
Version: 0.234

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com