

PHILIPS

Eridani Recessed
Light 3.5W

Recessed Lights

6500K

White

8720169332904



High quality LED light designed to last for years

Light up your space with Philips EyeComfort LED Downlight that provides a comfortable light source and ease to your eyes.

Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Light effect

- Uniform light distribution

Durability

- Long life span up to 15,000 hours

Highlights

Suitable for low ceilingsSlim design

Uniform light distribution

Throw light across your rooms in an even and uniform manner.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Plastic

Durability

- Number of switch cycles: 7,500
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 100 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Lamp current: 35 mA
- Efficacy: 71 lm/W

Power consumption

- Power factor: 0.45
- Power Consumption: 3.5

Product dimensions and weight

- Net weight: 0.036 kg
- Height: 4 cm
- Recessed distance: 90 mm

Service

- Warranty: 1 year(s)

Technical specifications

- Diameter: 90 mm
- Total lumen output fixture: 250
- Light color: 6500
- Mains power: AC 220-240
- Fixture dimmable: No
- IP code: IP20
- Class of protection: Class II – Double Insulated
- Number of light sources: 10

Packaging dimensions and weight

- EAN/UPC – product: 8720169332904
- Net weight: 0.04 kg
- Gross weight: 0.1 kg
- Height: 15.4 cm
- Length: 9.3 cm
- Width: 9.3 cm



Issue date: 2025-06-14
Version: 0.130

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com