

# PHILIPS

Buzzard Wall Light  
60W E27 No-bulb

myGarden

No bulb

Black

Water Resistant



17236/30/PN



## Create great outdoor moments

Bring the vintage look outside with this black edition wall lantern from Philips myGarden. The retro design is a stylish way to enjoy your outdoor moments. High quality materials and black finish fits perfectly with your personal style.

### Designed for outdoors

- High quality materials

### Special characteristics

- Weather proof

### Enjoy your outdoor life

- Create a stylish and welcoming atmosphere

# Highlights

## High quality materials

This Philips outdoor lamp is made of high quality materials with superior finishing. This ensures a solid and long lasting product which is resistant to corrosion and stains in all weather conditions

## Create a stylish atmosphere

This outdoor wall light is designed around the latest trends and lifestyles to blend effortlessly into your outdoor space and define the ambiance you have always desired.

## Weather proof



This Philips outdoor lamp is especially designed for humid outdoor environments and has undergone rigorous tests to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This lamp is designed with IP44: it is protected against splashing water, this product is most common and ideal for general outdoor use.

# Specifications

## Design and finishing

- Color: Black
- Material: Metal

## Extra feature/accessory incl.

- Fully weatherproof: Yes
- LED integrated: No

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Garden area

- Garden area: Garden & Patio

## Light characteristics

- Luminous Efficacy (rated) (Nom): 100

**Miscellaneous**

- Especially designed for: Garden, Patio
- Style: Classic
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

**Product dimensions and weight**

- Net weight: 0.867 kg
- Overall height: 290 mm
- Overall length: 130 mm
- Overall width: 175 mm

**Service**

- Warranty: 2 year(s)

**Technical specifications**

- Bulb technology: LED
- Mains power: 50 Hz
- Energy class included light source: no bulb included
- Fitting/cap: E27
- Wattage bulb included: -
- IP code: IP44
- Class of protection: Class I - Earthed
- Light source replaceable: Yes
- Number of light sources: 1

**The bulb**

- Software upgradable: No

**What's supported**

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

**Packaging dimensions & weight**

- EAN/UPC - product: 8718696156797
- Net weight: 0.87 kg
- Gross weight: 1.05 kg
- Height: 30.8 cm
- Length: 14.3 cm
- Width: 17.8 cm



Issue date: 2026-05-13  
Version: 0.554

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)