

PHILIPS

LED EM/Mains C-T9

LED

2000lm

6500K

G10q

8718699645359



Bright, stylish and slim interior lamp

MyCare LED Circular integrates a LED light source into a traditional fluorescent tube. It is specially designed to replace fluorescent circular tubes working on a G10q fitting. The lamp offers significant energy savings and a long lifetime, in a similar form factor.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: C-T9
- Socket: G10q
- Dimmable: No

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 30,000 h

Light characteristics

- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 2000 lm
- Warm-up time to 60% light: instant full light

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Efficacy: 100 lm/W

Packaging information

- EAN: 8718699645359
- EOC: 871869964535900
- Product title: LED Circular 20W 865 G10q AP

Power consumption

- Power factor: >0.5
- Voltage: 220-240 V
- Wattage: 20 W
- Wattage equivalent: 32 W

Product dimensions and weight

- Length: 29.8 cm

Technical specifications

- Frequency: 50-60 Hz
- Ballast Compatibility: EM/Mains

Packaging dimensions & weight

- EAN/UPC - product: 8718699645359
- Net weight: 0.11 kg
- Gross weight: 0.11 kg
- Height: 30.5 cm
- Length: 3.6 cm
- Width: 30.5 cm
- Material number (12NC): 929002011007



Issue date: 2024-03-29
Version: 0.249

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com