



# A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### High quality light

· No visible flicker

# Choose for a sustainable solution

• You can trust what the Philips packaging is saying.

# Create the right light for your home

· A simple LED for everyday use

# Highlights

# No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because

Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

#### No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light wonφηt fade.

# A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

# Specifications

#### **Bulb characteristics**

· Intended use: Indoor

· Lamp shape: Non directional bulb

· Socket: B22

Bulb Finish: Frosted

· Dimmable: No

#### **Durability**

Number of switch cycles: 50,000

• Nominal lifetime: 15,000

#### **Environmental**

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

#### **Light characteristics**

Beam angle: 180 degree(s)

· Color rendering index (CRI): 80

· Color temperature: 6500 K

· Nominal luminous flux: 806 lm

• Warm-up time to 60% light: 0.5

· Color Code: 865 | CCT of 6500K

Luminous Efficacy (rated) (Nom): 89 lm/W

#### Miscellaneous

· EyeComfort: No

#### **Packaging information**

• EAN: 8718699654078

• EOC: 871869965407800

 Product title: LEDBulb 9W B22 6500K 230V 1CT/6 AU

# **Power consumption**

• Power factor: 0.51

Voltage: 220-240 V

· Wattage equivalent: 50 W

· Power: 9 W

• Energy Consumption kWh/1000 h: 9

# Product dimensions and weight

• Overall height: 105 mm

· Overall length: 105 mm

• Overall width: 60 mm

### **Technical specifications**

• Frequency: 50-60

# Packaging dimensions & weight

• EAN/UPC - product: 8718699654078

· Net weight: 0.06 kg

· Gross weight: 0.08 kg

· Height: 10.7 cm

• Length: 6.1 cm

· Width: 6.1 cm



Issue date: 2025-11-29 Version: 0.299

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not

intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips