



State-of-the-art LED light bulb for the home

Philips LED light bulbs provide a beautiful, warm white light, a long lifetime, and immediate, significant energy savings. With its modern and elegant design, this dimmable bulb is the perfect replacement for your frosted traditional bulbs.

High quality light

- · No visible flicker
- Cool, energizing light

Choose for a sustainable solution

· You can trust what the Philips packaging is saying.

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

3500K [LED Lamps]



This bulb has a color temperature of 3500K providing you with a cool, energizing light, perfect for creating an

inviting ambiance to host friends or wind down with a book.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light wonφηt fade.

Specifications

Bulb characteristics

Intended use: Indoor
Lamp shape: A55
Socket: E27
Bulb Finish: Frosted
Dimmable: No

Durability

Number of switch cycles: 50,000Nominal lifetime: 10.000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

Beam angle: 150 degree(s)
Color rendering index (CRI): 80
Color temperature: 3000 K
Nominal luminous flux: 1350 lm
Warm-up time to 60% light: 1

Color Code: 830 | CCT of 3000K
Luminous Efficacy (rated) (Nom): 103 lm/W

Miscellaneous

· EyeComfort: No

Packaging information

EAN: 8718699688240EOC: 871869968824000

 Product title: ESS LEDBulb 13W E27 3000K 230V 3CT/4 AU

Power consumption

Power factor: 0.51Voltage: 220-240 VWattage equivalent: 77 W

• Power: 13 W

Energy Consumption kWh/1000 h: 13

Product dimensions and weight

Overall height: 120 mmOverall length: 120 mmOverall width: 60 mm

Rated values

· Rated peak intensity: 282 cd

Technical specifications

• Frequency: 50-60

Packaging dimensions & weight [ESS LEDBulb 13W E27 3000K 230V 3CT/4 AUI

• EAN/UPC - product: 8718699688240

Net weight: 0.17 kg
Gross weight: 0.2 kg
Height: 9.9 cm
Length: 5.8 cm
Width: 16.4 cm

Packaging dimensions & weight [ESS LEDBulb 13W E27 3000K 230V 3CT/4 AUI

• EAN/UPC - product: 8718699688240

Gross weight: 0.18 kgHeight: 12.6 cmLength: 6.1 cmWidth: 14.9 cm

· Net weight: 0.13 kg



Issue date: 2025-12-13 Version: 0.237 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N V