

PHILIPS

Bulb

E14

Clear

8718699754730



Tubular T25L

Tubular lamp designed for cooker hood use.

Specifications

Bulb characteristics

- Socket: E14
- Lamp shape code: T25L

Durability

- Average life (at 2.7 hrs/day): 1 year(s)
- Nominal lifetime: 1,000

Light characteristics

- Application: Special application, General light
- Color rendering index (CRI): 100
- Color temperature: 2700 K
- Nominal luminous flux: 424 lm
- Starting time: 0.0 s

Luminaire fit

- Shape: T25L

Power consumption

- Voltage: 230 – 240 V
- Power: 40
- Energy Consumption kWh/1000 h: 40

Technical specifications

- Lamp holder: E14
- Number of light sources: 2

Packaging dimensions & weight [40W E14 240V T25L CL CH 2PF/10]

- EAN/UPC – product: 8718699754730
- Net weight: 0.03 kg
- Gross weight: 0.04 kg
- Height: 8.6 cm
- Length: 2.6 cm
- Width: 5.2 cm

Packaging dimensions & weight [40W E14 240V T25L CL CH 2PF/6 SRT]

- EAN/UPC – product: 8718699754730
- Net weight: 0.03 kg
- Gross weight: 0.04 kg
- Height: 8.6 cm
- Length: 2.6 cm
- Width: 5.2 cm



Issue date: 2025-12-13
Version: 0.103

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com