

# PHILIPS

Bulb

B22

Clear

8718699754754



## Tubular T25


Tubular lamp designed for cooker hood use.

**Superior light quality**

- For use in cooker hoods

# Highlights

## For use in cooker hoods



This Philips appliance bulb is designed for use in cooker hoods, promising a long, useful life. Can also be used in other applications that require a slim fit light bulb.

# Specifications

## Bulb characteristics

- Socket: B22
- Lamp shape code: T25

## Durability

- Average life (at 2.7 hrs/day): 1 year(s)
- Nominal lifetime: 1,000

## Light characteristics

- Application: Special application, General light
- Color rendering index (CRI): 100
- Color temperature: 2700 K
- Nominal luminous flux: 90 lm
- Starting time: 0.0 s

## Luminaire fit

- Shape: Tubular

## Power consumption

- Voltage: 230 – 240 V
- Power Consumption: 15
- Energy Consumption kWh/1000 h: 15

## Technical specifications

- Lamp holder: B22
- Number of light sources: 2

## Packaging dimensions & weight

- EAN/UPC – product: 8718699754754
- Net weight: 0.03 kg
- Gross weight: 0.03 kg
- Height: 6 cm
- Length: 2.6 cm
- Width: 5.2 cm



Issue date: 2025-08-30  
Version: 0.86

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)