



Wi-Fi LEDSTRIP 2M 1600LM STARTKIT TYPE-I

The WiZ 2-metre LED strip starter kit gives you everything you need to get bright, full-color smart light. Cut the flexible strip to size to add indirect, linear lighting to any space. Use with the WiZ app or your voice to dim and brighten or use preset light modes on Wi-Fi setups.

PRODUCT HIGHLIGHTS

- Full color
- Low Voltage
- IP20/Pu-coating



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.




Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control, or by using the existing wall switch to toggle between two favorite modes. Works with Google Home, Alexa and Siri Shortcuts.



SPECIFICATIONS

DESIGN AND FINISHING

Color: White
Material: Plastic

EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: No
Dimmable with remote control: No
LED integrated: Yes
On/off switch on wire: No
Power adapter included: Yes
Remote control included: No

LIGHT CHARACTERISTICS

Color rendering index (CRI): 80

LIGHTSTRIP

Output Power: 12VDC, 20W Max.

MISCELLANEOUS

Especially designed for: Functional

POWER CONSUMPTION

Voltage: 100-240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.24 kg
Height: 0.22 cm
Length: 200 cm
Width: 1.2 cm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Lifetime up to: 15,000 h
Total lumen output fixture: 1600
Light color: 2700-6500 (RGB)
Fixture dimmable: Yes
LED: Yes
Built in LED: Yes
Wattage bulb included: 20
IP code: IP20
Class of protection: Class III



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.