

LED Strip Extension 1m

Extend your WiZ LED strip up to 10 metres with the flexible, full-color 1-metre extension strip, which lets you bring even more color to your home.

PRODUCT HIGHLIGHTS

- Full color
- 1M LED strip
- IP20/Plastic



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.




Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control, or by using the existing wall switch to toggle between two favorite modes. Works with Google Home, Alexa and Siri Shortcuts.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor

DESIGN AND FINISHING

Color: White

Material: Plastic

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)

Lumen maintenance factor: 70%

Number of switch cycles: 50,000

Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: No

LED integrated: Yes

On/off switch on wire: No

Power adapter included: No

Remote control included: No

Solar Energy: No

Warm glow dimmable light: No

LIGHT CHARACTERISTICS

Color consistency: 6 SDCM

Color rendering index (CRI): ≥ 80

Color temperature: 2700-6500 K

Warm-up time to 60% light: 2

Luminous Efficacy (rated) (Nom): 80

STRING LIGHT/LIGHTSTRIP

Extendibility: Yes

Output Power: 12 VDC

MISCELLANEOUS

Especially designed for: Kitchen
Bedroom Living Room Children's
room

OTHER CHARACTERISTICS

Lamp current: 800 mA

POWER CONSUMPTION

Voltage: 12 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.05 kg

Overall height: 2.2 mm

Overall length: 1,000 mm

Overall width: 12 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Total lumen output fixture: 440/880

Bulb technology: LED

Light color: Coloured and white light
(RGBW)

Fixture dimmable: Yes

Wattage bulb included: 11

IP code: IP20 | Finger-protected

Class of protection: Class III - Safe

Extra Low Voltage

THE BULB

Software upgradable: Yes

WHAT'S SUPPORTED

Compatible with Effects: Yes

WiFi: 802.11b/g/n

Defined support period: Minimum of
60 months after introduction date

Max. number of accessories: 9999

Compatible operating systems: iOS
Android

Communication protocol: Bluetooth
WiFi (2.4GHz)

Compatibility with 3rd party systems:

Alexa Enki Google Home Homey

IFTTT Matter Samsung Smartthings

Siri Shortcuts

Matter functionality: Via 3rd party
hubs (Wi-Fi)

PACKAGING DIMENSIONS & WEIGHT

EAN/UPC - product: 8719514261082

Net weight: 0.05 kg

Gross weight: 0.12 kg

Height: 16 cm

Length: 4.5 cm

Width: 7.5 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.