

# PHILIPS

Spot 50W PAR16  
GU10

LED

3000K

405lm

15000h

Dimming

8719514274099



## Durable LED accent lighting with a focused bright beam

This Philips LED spot provides a dimmable, focused bright beam, an exceptionally long life, and significant energy savings. This spot is the perfect long-lasting replacement for 50W spots with a GU10 cap.

### High quality light

- Cool, energizing light

### Choose for a sustainable solution

- Saves up to 80% Energy

### Create the right light for your home

- Perfect for accent lighting and general purpose lighting

# Highlights

## 3500K [LED Lamps]



This bulb has a color temperature of 3500K providing you with a cool, energizing light, perfect for creating an inviting ambiance to host friends or wind down with a book.

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

## 60° beam - spot



Modern lighting with a familiar extra wide angle light output (60 degrees), this LED spot is suitable for both accent lighting and general purpose lighting. It can be used in recessed cans and track light fixtures, and is ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Dimmable: Yes

## Bulb dimensions

- Height: 5.4 cm
- Width: 5 cm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h

## Light characteristics

- Beam angle: 60 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 405 lm
- Warm-up time to 60% light: instant full light
- Color Code: 830 | CCT of 3000K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 81 lm/W

## Packaging information

- EAN: 8719514274099
- EOC: 871951427409900
- Product title: LEDClassic 5-50W GU10 830 60D D 1PF/10

## Power consumption

- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 5 W
- Wattage equivalent: 50 W

## Product dimensions and weight

- Length: 5.4 cm

## Rated values

- Rated peak intensity: 450 cd

## Technical specifications

- Frequency: 50-60 Hz

**Packaging dimensions & weight**

- EAN/UPC - product: 8719514274099
- Net weight: 0.05 kg
- Gross weight: 0.07 kg
- Height: 6 cm
- Length: 5.1 cm
- Width: 5.1 cm
- Material number (12NC): 929001364469



Issue date: 2024-03-29  
Version: 0.29

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)