



Experience dimmable, warm white LED light

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Choose for a sustainable solution

• Long life bulbs - Lasts up to 15 years

Light beyond illumination

• Dimmable

High quality LED light that lasts for decades

• Designed for the comfort of your eyes

Highlights

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Non directional bulb

Socket: B22Dimmable: YesBulb Finish: FrostedBulb Material: Plastic

Durability

• Number of switch cycles: 50,000

• Ambient temperature range: -20 to +45 °C

· Nominal lifetime: 15,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

• Beam angle: 150 degree(s)

· Color rendering index (CRI): 90

· Color temperature: 2700 K

· Nominal luminous flux: 1055 lm

• Warm-up time to 60% light: 0.5 s

• Color Code: 927 | CCT of 2700K

• Correlated Color Temperature (Nom): 2700 K

· Luminous Flux: 1,055 lm

 Luminous Efficacy (rated) (Nom): 100 lm/W

Miscellaneous

EyeComfort: Yes

· LED Innovations: EyeComfort

• Extra Features: Dimmable

Other characteristics

• EU RoHS compliant: Yes

Packaging information

• EAN: 8719514333673

• EOC: 871951433367300

 Product title: LEDBulb 10.5-75W B22 2700K D 1PF/6 AU

Power

· Power Factor (Fraction): 0.9

Power consumption

Power factor: 0.9Voltage: 220-240 V

Wattage equivalent: 75 WPower Consumption: 10.5 W

• Energy Consumption kWh/1000 h: 11

Product dimensions and weight

Overall height: 110 mmOverall length: 110 mmOverall width: 60 mm

Rated values

• Rated lifetime: 15,000

Technical specifications

Frequency: 50-60Diameter: 60 mm

• Dimmable: Only with specific

dimmers
• Cap-Base: B22

Packaging dimensions & weight

• EAN/UPC - product: 8719514333673

Net weight: 0.08 kgGross weight: 0.09 kgHeight: 13.7 cm

Length: 6.1 cmWidth: 6.1 cm



Issue date: 2025-10-22 Version: 0.385

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips