

PHILIPS

Spot 150W R7S

LED

3000K

2460lm

15000h

Dimming

8719514372979



Dimmable linear LED light with a 300 degree beam

This innovative Linear LED is the perfect replacement for halogen R7S lamps, while far surpassing them in terms of energy efficiency.

High quality light

- Cool, energizing light

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen spot
- Similar shape and size as halogen linear

Highlights

3500K [LED Lamps]



This bulb has a color temperature of 3500K providing you with a cool, energizing light, perfect for creating an inviting ambiance to host friends or wind down with a book.

Replaces halogen reflector



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, LED capsule. The perfect sustainable replacement for traditional halogen spots.

Replaces linear halogen



With its beautifully shaped design and familiar dimensions, this standard modern lighting, LED linear is the perfect sustainable replacement for traditional halogen linears.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: R7s
- Dimmable: Yes
- Bulb Finish: Clear
- Bulb Material: Plastic

Bulb dimensions

- Height: 11.8 cm
- Width: 4.2 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h
- Ambient temperature range: -20 to +45 °C

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 2460 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 830 | CCT of 3000K
- Correlated Color Temperature (Nom): 3000 K
- Luminous Flux: 2,460 lm
- Luminous Efficacy (rated) (Nom): 140 lm/W

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 140 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8719514372979
- EOC: 871951437297900
- Product title: LED 17.5-150W R7S 118mm 830 D 1pk AU

Power

- Power Factor (Fraction): 0.9

Power consumption

- Power factor: 0.9
- Voltage: 220-240 V
- Wattage: 17.5 W
- Wattage equivalent: 150 W
- Power Consumption: 17.5 W

Product dimensions and weight

- Length: 11.8 cm

Rated values

- Rated lifetime: 15,000 h

Technical specifications

- Frequency: 50-60 Hz
- Dimmable: Only with specific dimmers
- Cap-Base: R7s

Packaging dimensions & weight

- EAN/UPC – product: 8719514372979
- Net weight: 0.1 kg
- Gross weight: 0.1 kg
- Height: 12 cm
- Length: 3 cm
- Width: 4.2 cm
- Material number (12NC): 929002016679



Issue date: 2024-03-29
Version: 0.21

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com