

PHILIPS

Reflector 13W PAR38
E27 2700K NonDim

LED

2700K

1200lm

15000h

8719514406933



Smart lighting for you daily living

PAR38 with daylight and motion sensor to provide an easy smart lighting for you

Light beyond illumination

- Instant on
- Built-in automatic on/off light sensor

Highlights

Instant on Day and night sensor



With its built-in automatic light sensor, this bulb switches on automatically after dusk and off after dawn.

Specifications

General

- Suitable For Accent Lighting: Yes

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E27
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Plastic

Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 40 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 1200 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 927 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700
- Luminous Flux: 1,200 lm
- Luminous Efficacy (rated) (Nom): 92

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 8719514406933
- EOC: 871951440693300
- Product title: 13PAR38/S/120W/927 40D E27 ND/G/110-277V

Power

- Power Factor (Fraction): 0.7

Power consumption

- Power factor: 0.7
- Voltage: 110-277 V
- Wattage equivalent: 120
- Power: 13

Product dimensions and weight

- Overall height: 137 mm
- Overall length: 137 mm
- Overall width: 122 mm

Rated values

- Rated lifetime: 15,000
- Rated peak intensity: 2231 cd

Technical specifications

- Frequency: 50-60
- Diameter: 122 mm
- Bulb technology: LED
- Dimmable: No
- Line Frequency: 50 to 60
- Cap-Base: E27

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions & weight

- EAN/UPC - product: 8719514406933
- Net weight: 0.31 kg
- Gross weight: 0.69 kg
- Height: 15.7 cm
- Length: 13 cm
- Width: 13 cm



Issue date: 2026-04-15
Version: 0.67

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com