

PHILIPS

Downlight

Recessed Lights

3000/4000/6500K

White

Dimmable



8719514443679



Control your light Experience with ease

Light up your space with Philips EyeComfort LED Downlight that provides a comfortable light source and ease to your eyes.

Light effect

- Bright light with uniform distribution

Control

- Dimmable

Durability

- Long life span up to 20,000 hours

Highlights

Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Dimmable

Allows you to change the mood by reducing LED brightness levels, from bright white light, to a cozy glow – just like traditional lamps.

Long life span up to 20,000 hours

Philips LED technology extends your product's lifetime up to 20,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Metal, Plastic

Durability

- Number of switch cycles: 15,000
- Nominal lifetime: 30,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 100 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700–4000–6500 K
- Luminous Efficacy (rated) (Nom): 106 lm/W

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- Extra Features: Dimmable

Other characteristics

- Lamp current: 38 mA

Product dimensions and weight

- Net weight: 0.23 kg
- Recessed distance: 0 mm
- Overall height: 56 mm
- Overall length: 114 mm
- Overall width: 114 mm
- Recessed Ceiling cutout: 9.0 cm x 9.0 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Diameter: 114 mm
- Total lumen output fixture: 800
- Light color: 3000/4000/6500
- Mains power: AC 220–240
- Fixture dimmable: Yes
- Wattage bulb included: 7.5
- IP code: IP40 | Wire-protected
- Class of protection: Class II – Double Insulated

Packaging dimensions & weight

- EAN/UPC – product: 8719514443679
- Net weight: 1.84 kg
- Gross weight: 2.04 kg
- Height: 24.8 cm
- Length: 13.6 cm
- Width: 24.8 cm



Issue date: 2025-09-03
Version: 0.108

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com