

PHILIPS

Downlight

Recessed Lights

3000/4000/6500K

White

Dimmable; Water Resistant



8719514478794



Comfortable light with a slimmer fit

Light up your space with Philips EyeComfort LED Downlight that provides a comfortable light source and ease to your eyes.

Easy to experience

- Hassle-free installation that does not require wiring.

Light effect

- Bright light with uniform distribution

Control

- Dimmable

Highlights

Easy installation

Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Dimmable

Allows you to change the mood by reducing LED brightness levels, from bright white light, to a cozy glow - just like traditional lamps.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

Design and finishing

- Color: White
- Material: Metal, Plastic

Durability

- Average life (at 2.7 hrs/day): 20 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 10,000
- Nominal lifetime: 20,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 100 degree(s)
- Color consistency: 5 SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700-4000-6500 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 111 lm/W

Miscellaneous

- Especially designed for: Bathroom, Bedroom, Living Room, Dining Room, Kitchen, Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- Extra Features: Dimmable, Water Resistant

Other characteristics

- Lamp current: 45 mA

Power consumption

- Power factor: 0.8

Product dimensions and weight

- Net weight: 0.22 kg
- Recessed distance: 0 mm
- Overall height: 56 mm
- Overall length: 114 mm
- Overall width: 114 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Diameter: 114 mm
- Total lumen output fixture: 1000
- Light color: 3000/4000/6500
- Mains power: AC 220-240
- Fixture dimmable: Yes
- Wattage bulb included: 9
- IP code: IP54 | Dust-accumulation-protected and splash-proof
- Class of protection: Class II - Double Insulated

Packaging dimensions & weight

- EAN/UPC - product: 8719514478794
- Net weight: 0.22 kg
- Gross weight: 0.26 kg
- Height: 12.4 cm
- Length: 6.8 cm
- Width: 12.4 cm



Issue date: 2025-08-02
Version: 0.127

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com