




Pole Floor Light

Enjoy colored, wide-angle wall-wash effects with this Pole LED floor light. Standing tall in the corner, it creates ambience thanks to dual zone lighting producing a soft, gradient light. With its foot removed, placed horizontally under your couch or behind your TV, it invites you to unwind with your family.

PRODUCT HIGHLIGHTS

- Full color
- Versatile bar light
- Dual zone light effect



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and have lights turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.




Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.




Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control, or by using the existing wall switch to toggle between two favorite modes. Works with Google Home, Alexa and Siri Shortcuts.



Enjoy a dual light zone effect with a slim design

Create a rainbow of color combinations that extend the ambience to every corner. Play with dynamic light modes to create the ambience that fits your mood, upper and lower parts of the lamp emit different colors.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Dimmable: Yes

DESIGN AND FINISHING

Color: White
Material: Plastic

DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 25,000

EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes
LED integrated: Yes
On/off switch on wire: No
Remote control included: No

LIGHT CHARACTERISTICS

Color consistency: 6 SDCM
Color rendering index (CRI): ≥ 80
Color temperature: 2200-6500 K
Warm-up time to 60% light: 2
Luminous Efficacy (rated) (Nom): 83

MISCELLANEOUS

Especially designed for: Living Room
Dining Room Bedroom Children's room

OTHER CHARACTERISTICS

Lamp current: 120 mA

POWER CONSUMPTION

Power factor: 0.5
Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 1.5 kg
Overall height: 1,500 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Diameter: 180 mm
Total lumen output fixture: 1080
Light color: Coloured and white light (RGBW)
Wattage bulb included: 13
IP code: IP20 | Finger-protected
Class of protection: Class II - Double Insulated

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth WiFi (2.4GHz)
Compatibility with 3rd party systems: Alexa Google Home IFTTT
Klikaanklikuit Matter Samsung Smartthings Sonos

PACKAGING DIMENSIONS & WEIGHT

EAN/UPC - product: 8719514554337
Net weight: 1.31 kg
Gross weight: 1.99 kg
Height: 12.8 cm
Length: 118.1 cm
Width: 20.5 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.