




Mobile Portable Light

Turn your personal space into all kinds of special by exploring endless combinations of soft light and colorful gradients. Bring Mobile LED light along, anywhere inside or even outside your home and make your cozy corner truly inviting.

PRODUCT HIGHLIGHTS

- Full color
- Dual zone light effect
- Touch panel control



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and have lights turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Dual zone light effect, everywhere

Try all kinds of light colors to create a unique gradient that's really you. Play with dynamic light modes to create Scenes that fit your mood, upper and lower parts of the lamp emit different colors.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: Round
Dimmable: Yes

DESIGN AND FINISHING

Color: White
Material: Plastic

DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 25,000

EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: Not adjustable
Dimmable with remote control: Yes
LED integrated: Yes
On/off switch on wire: No
Remote control included: No

LIGHT CHARACTERISTICS

Color consistency: 6 SDCM
Color rendering index (CRI): ≥80
Color temperature: 2200-6500 K
Warm-up time to 60% light: 2
Luminous Efficacy (rated) (Nom): 29

MISCELLANEOUS

Especially designed for: Bedroom
Dining Room Living Room Outside
Children's room

OTHER CHARACTERISTICS

Lamp current: 90 mA

POWER CONSUMPTION

Power factor: 0.6
Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.65 kg
Overall height: 193 mm
Overall length: 116 mm
Overall width: 116 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Diameter: 116 mm
Total lumen output fixture: 400
Light color: Coloured and white light (RGBW)
Wattage bulb included: 13.5
IP code: IP20 | Finger-protected
Class of protection: Class II - Double Insulated

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: 802.11b/g/n
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth WiFi (2.4GHz)
Compatibility with 3rd party systems: Alexa Enki Google Home Homey IFTTT Matter Samsung Smartthings Siri Shortcuts

PACKAGING DIMENSIONS & WEIGHT

EAN/UPC - product: 8719514554351
Net weight: 0.65 kg
Gross weight: 1.1 kg
Height: 27.2 cm
Length: 16.5 cm
Width: 16.5 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.