



Gradient Light Bars

Bring dynamic lighting to your home with the WiZ Gradient Light Bars (2 included). Enjoy RGBIC technology for multi-color displays. Position them horizontally, vertically, or behind your TV to create the perfect ambiance. Pre-set modes let you switch among dynamic, static or customizable light modes. You can even have the lights pulse to music, or sync with your TV screen (HDMI Sync Box needed).


PRODUCT HIGHLIGHTS

- Multiple colors at once
- Multiple placement options
- Sync with TV (Sync Box needed)




Control with any Matter smart home platform

This product is Matter certified, allowing easy control through Google Home, Amazon Alexa, Apple Home, or any other Matter-based smart home platform of your choice.



Use it how and where you like

Place our Gradient Light Bars horizontally or vertically on a TV cabinet or desk, or mount them behind your TV/monitor using the magnetic back brackets. With a 100° rotation, you can spread the lighting effects to create the perfect atmosphere.



Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Sync Lights to Music

Dive into the rhythm with our Music Sync feature. Effortlessly synchronize your lights to your favorite tunes. Just remember, keep your mobile device near the speaker for perfect harmony between sound and light.



Immersive surround-lighting

Sync your lights with music and video using the HDMI Sync Box to enhance your entertainment experience. Perfect for movies and gaming, the Sync feature creates a truly immersive, theater-like atmosphere that brings your content to life.



Static and dynamic light modes to lift your mood

Choose from millions of colors or from the set of light modes we've designed for you. With so many options, you can bring the magic to all your holidays, parties, intimate get-togethers, and daily vibes!



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Dimmable: Yes

DESIGN AND FINISHING

Color: Black
Material: Plastic

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes
LED integrated: Yes
On/off switch on wire: Yes
Remote control included: No

LIGHT CHARACTERISTICS

Color rendering index (CRI): -
Color temperature: NA
Warm-up time to 60% light: 2

MISCELLANEOUS

Especially designed for: Living Room
Dining Room Bedroom Children's
room

OTHER CHARACTERISTICS

Lamp current: 49 mA

POWER CONSUMPTION

Power factor: 0.7
Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.545 kg
Overall height: 50.4 mm
Overall length: 318 mm
Overall width: 90 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Total lumen output fixture: NA
Light color: Gradient coloured light
(RGBIC)
Wattage bulb included: 8.2
IP code: IP20 | Finger-protected
Class of protection: Class II - Double
Insulated

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: Wireless G
Defined support period: Minimum of
60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS & WEIGHT

EAN/UPC - product: 8719514865358
Net weight: 0.55 kg
Gross weight: 0.81 kg
Height: 17.1 cm
Length: 7.4 cm
Width: 41.3 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.