



Gradient Floor Light

Transform your space with the WiZ Gradient Floor Light. Enjoy RGBIC technology for stunning, multi-color displays that bathe the room in light. Its sleek, minimalist design fits into any corner, while customizable pre-set modes let you choose between dynamic animations or soft, static glows. You can even have your light pulse to music, or match the colors of your TV screen (HDMI Sync Box needed).

PRODUCT HIGHLIGHTS

- Multiple colors at once
- Sleek and minimalist design
- Sync with TV (Sync Box needed)



Control with any Matter smart home platform

This product is Matter certified, allowing easy control through Google Home, Amazon Alexa, Apple Home, or any other Matter-based smart home platform of your choice.



Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Sync Lights to Music

Dive into the rhythm with our Music Sync feature. Effortlessly synchronize your lights to your favorite tunes. Just remember, keep your mobile device near the speaker for perfect harmony between sound and light.



Immersive surround-lighting

Sync your lights with video (HDMI Sync Box required) and music to elevate your home entertainment. Perfect for movies and gaming, the Sync feature creates a fully immersive, theater-like experience that brings your content to life.



Static and dynamic light modes to lift your mood

Choose from millions of colors or from the set of light modes we've designed for you. With so many options, you can bring the magic to all your holidays, parties, intimate get-togethers, and daily vibes!



Stunning gradient light effect

Experience the beauty of gradient lighting, where multiple colors flow seamlessly together to create a mesmerizing light effect. Add vibrant energy to any room with this dynamic design.



SPECIFICATIONS

GENERAL

Cable color: black

BULB CHARACTERISTICS

Intended use: Indoor

Dimmable: Yes

DESIGN AND FINISHING

Color: Black

Material: Aluminium

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)

Lumen maintenance factor: 70%

Number of switch cycles: 50,000

Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes

LED integrated: Yes

On/off switch on wire: No

Remote control included: No

Solar Energy: No

Warm glow dimmable light: No

LIGHT CHARACTERISTICS

Color rendering index (CRI): -

Color temperature: NA

Warm-up time to 60% light: 2

MISCELLANEOUS

Especially designed for: Bedroom

Dining Room Living Room Children's room

OTHER CHARACTERISTICS

Lamp current: 58 mA

POWER CONSUMPTION

Power factor: 0.7

Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 1.347 kg

Overall length: 1,355 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Diameter: 90 mm

Total lumen output fixture: NA

Bulb technology: LED

Light color: Gradient coloured light (RGBIC)

Wattage bulb included: 9.7

IP code: IP20 | Finger-protected

Class of protection: Class II - Double

Insulated

THE BULB

Software upgradable: Yes

WHAT'S SUPPORTED

Compatible with Effects: Yes

WiFi: 802.11b/g/n

Defined support period: Minimum of 60 months after introduction date

Max. number of accessories: 9999

Compatible operating systems: iOS Android

Communication protocol: Bluetooth WiFi (2.4GHz)

Compatibility with 3rd party systems:

Alexa Enki Google Home Homey

IFTTT Matter Samsung Smartthings

Siri Shortcuts

Matter functionality: Via 3rd party hubs (Wi-Fi)

PACKAGING DIMENSIONS & WEIGHT

EAN/UPC - product: 8719514865419

Net weight: 1.33 kg

Gross weight: 3.01 kg

Height: 14.8 cm

Length: 143.4 cm

Width: 14.3 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.