



# Filament Globe Clear 40W G95 E27

WiZ filament bulbs are meant to be seen—they look great even when they're turned off. But wait until you turn them on! These dimmable transparent globes of light bathe every corner of your room with all the colors of the rainbow and every shade of white from warm to cool. Enjoy the classic look of vintage incadescent filament bulbs while reaping the energy-saving benefits of LED. All Wi-Fi controllable, of course, using the WiZ app, WiZ remote, or your voice.

## **PRODUCT HIGHLIGHTS**

- Full color smart bulb
- Up to 470 lumens
- Easy plug and play
- Control with app or voice

EAN: 8720169072190 wizconnected.com





#### Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



#### Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



#### Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



### Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



## Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



#### Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control, or by using the existing wall switch to toggle between two favorite modes. Works with Google Home, Alexa and Siri Shortcuts.

EAN: 8720169072190 wizconnected.com



## **SPECIFICATIONS**

#### **BULB CHARACTERISTICS**

Intended use: Indoor Lamp shape: G95 Socket: E27 Type of glass: Clear

Type of glass: Clear Dimmable: Yes

#### **BULB DIMENSIONS**

Weight: 0.065 kg

#### **DURABILITY**

Average life (at 2.7 hrs/day): 15 year(s) Lumen maintenance factor: 70% Number of switch cycles: 20,000 Nominal lifetime: 15.000

#### LIGHT CHARACTERISTICS

Color consistency: 6 SDCM Color rendering index (CRI): ≥80 Color temperature: 2200-6500 K Light Color Category: Full color Nominal luminous flux: 470 lm

Starting time: <0.5 s

Warm-up time to 60% light: instant

full ligh

Luminous Efficacy (rated) (Nom): 74

Im/W

#### **OTHER CHARACTERISTICS**

Lamp current: 47 mA

#### **PACKAGING INFORMATION**

EAN: 8720169072190 EOC: 872016907219000

Product title: Wi-Fi BLE 40W G95 E27

822-65 RGB CL 1PF

#### **POWER CONSUMPTION**

Power factor: 0.5 Voltage: 220-240 V Wattage equivalent: 40 W Energy Efficiency Label (EEL): G Power Consumption: 6.3 W

Energy Consumption kWh/1000 h: 7

#### PRODUCT DIMENSIONS AND WEIGHT

Overall height: 142 mm Overall length: 142 mm Overall width: 95 mm

#### **RATED VALUES**

Rated lifetime: 15,000 Rated luminous flux: 470 lm

Rated power: 6.3 W

#### **TECHNICAL SPECIFICATIONS**

Frequency: 50-60

EPREL Registration Number: 1901106 Flux measurement reference: Sphere

#### **WHAT'S SUPPORTED**

Compatible with Effects: Yes

WiFi: Wireless G

Defined support period: Minimum of 60 months after introduction date Max. number of accessories: 9999 Communication protocol: Bluetooth

WiFi (2.4GHz)

#### **PACKAGING DIMENSIONS & WEIGHT**

EAN/UPC - product: 8720169072190

Net weight: 0.07 kg Gross weight: 0.14 kg Height: 18.5 cm Length: 10.5 cm

Width: 10.5 cm

### (s)ignify

© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

EAN: 8720169072190 wizconnected.com