



Globe 75W G95 E27

Think global and act local with these smart LED globe-shaped bulbs. So many uses around the house—vanity and bathroom lighting, playful pendants, special chandeliers, and more. Choose from hundreds of shades of white light from cozy to cool, or schedule to automatically adjust to match your ever-changing needs and moods. All Wi-Fi controllable using the WiZ app, WiZ remote, or your voice.

PRODUCT HIGHLIGHTS

- Tunable white smart bulb
- Up to 1055 lumens
- Easy plug and play
- Control with app or voice




Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Control with any Matter smart home platform

This product is Matter certified, allowing easy control through Google Home, Amazon Alexa, Apple Home, or any other Matter-based smart home platform of your choice.




Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Activate devices with motion without using a sensor

WiZ's SpaceSense technology transforms your devices into motion sensors. Activate the SpaceSense feature in the WiZ app and have lights and devices turn on and off automatically, with motion detection. A minimum of two WiZ devices in a room is needed for the SpaceSense feature to work.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: G95
Socket: E27
Type of glass: Frosted
Dimmable: Yes

BULB DIMENSIONS

Weight: 0.09 kg

DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 25,000

LIGHT CHARACTERISTICS

Color consistency: 6 SDCM
Color rendering index (CRI): ≥ 80
Color temperature: 2700-6500 K
Light Color Category: Tunable white
Nominal luminous flux: 1055 lm
Starting time: < 0.5 s
Warm-up time to 60% light: instant full light
Luminous Efficacy (rated) (Nom): 95 lm/W

OTHER CHARACTERISTICS

Lamp current: 75 mA

PACKAGING INFORMATION

EAN: 8720169076884
EOC: 872016907688400
Product title: Wi-Fi BLE 75W G95 E27
827-65 TW 1PF/6

POWER CONSUMPTION

Power factor: 0.5
Voltage: AC 220-240 V
Wattage equivalent: 75 W
Energy Efficiency Label (EEL): F
Power Consumption: 11 W
Energy Consumption kWh/1000 h: 11

PRODUCT DIMENSIONS AND WEIGHT

Overall height: 139 mm
Overall length: 139 mm
Overall width: 95 mm

RATED VALUES

Rated lifetime: 25,000
Rated luminous flux: 1055 lm
Rated power: 11 W

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Frequency: 50-60
EPREL Registration Number: 1877822
Flux measurement reference: Sphere

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS & WEIGHT

EAN/UPC - product: 8720169076884
Net weight: 0.1 kg
Gross weight: 0.21 kg
Height: 18.5 cm
Length: 10.5 cm
Width: 10.5 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.