

PHILIPS

Jivix Ground Spots/Spike 1.4W

Outdoor luminaires

2700K

Black

Sensor;Solar;Water Resistant



8720169269132



Long-lasting solar-powered garden light for all seasons

Philips Jivix spotlight is a reliable solar light that lasts longer time, reduces energy consumption and supports sustainability.

Easy installation

- No wiring required

Sustainable light solutions

- Long lifetime up to 15,000 hours

Advanced LED light

- High quality LED light

Designed for outdoors

- IP44 - weather proof

Highlights

No wiring required



This light is powered entirely by solar energy. No wiring is needed, making these lights easy to position and reposition anywhere in your garden or other outdoor area.

Long lifetime up to 15,000 hours



Reliable high-quality LED light lasts up to 15,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

High quality LED light



These LED lights use a unique technology developed by Philips. They turn on instantly and produce optimal light output that brings out the vivid colors in your garden.

IP44 - weather proof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water—perfect for general outdoor use.

Specifications

Design and finishing

- Color: Black
- Material: Plastic

Durability

- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Anti rust anti dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: Yes
- Diffused light effect: Yes
- Fully weatherproof: Yes
- Motion sensor: No
- Premium quality material: Yes
- Solar Energy: Yes
- Warm glow dimmable light: No
- Centerpiece: No

Garden area

- Garden area: Garden & Patio

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: 150
- Light color: Warm white light
- Mains power: 4 V
- Fixture dimmable: No
- Energy class included light source: not applicable
- Maximum wattage replacement bulb: 1.4
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class III - Safe Extra Low Voltage

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 2700 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Ground Spots/Spikes
- EyeComfort: No
- Extra Features: Sensor, Solar, Water Resistant

Packaging dimensions & weight

- EAN/UPC - product: 8720169269132
- Net weight: 0.32 kg
- Gross weight: 0.42 kg
- Height: 18.5 cm
- Length: 11.5 cm
- Width: 14.5 cm

Product dimensions and weight

- Net weight: 0.316 kg
- Overall height: 323 mm
- Overall length: 151 mm
- Overall width: 105 mm



Issue date: 2025-12-10
Version: 0.290

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com