

PHILIPS

Lois Wall Lights 14W

UltraEfficient

5000K

Anthracite

Water Resistant



8720169365407



Our most energy-efficient LED lights yet

Philips Lois Ultra Efficient outdoor flood lights use groundbreaking new technology to cut carbon emissions, reduce material waste, and lower energy usage. With an amazing lifetime of 50,000 hours, these lights last more than two times longer than Philips LED outdoor equivalents, and uses 50% less energy--just the thing for a more sustainable planet.

Sustainable light solutions

- Long lifetime up to 50,000 hours
- Ultra Efficient

Premium quality

- Durable design with PowerShield coating

Designed for outdoors

- IP44 - weather proof

Special characteristics

- Motion sensor, for convenience and reassurance

High quality light

- High light output

Highlights

Long lifetime up to 50,000 hours



Reliable high-quality LED light lasts up to 50,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

Ultra Efficient



Consumes at least 50% less energy as compared with equivalent standard LED lights from Philips.

Durable design



Protected by PowerShield To keep your outdoor lights in excellent condition, we use a high-performance powder coating powered by Interpon, an AkzoNobel brand. Tougher than traditional paints, it protects against fading, scratches, dents, and rust for long-lasting beauty and performance.

IP44 - weather proof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water—perfect for general outdoor use.

Motion sensor, for convenience and reassurance



A motion sensor is included to welcome you when you return home or let you know when someone's on their way.

High light output

Brighten up your home with high quality light

Specifications

Design and finishing

- Color: Anthracite
- Material: Metal

Durability

- Nominal lifetime: 50,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Adjustable – rise and fall
- Anti rust anti dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: No
- Centerpiece: No

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 5000 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- LED Innovations: UltraEfficient
- Extra Features: Water Resistant

Power consumption

- Power: 14

Product dimensions and weight

- Net weight: 0.404 kg
- Overall height: 190 mm
- Overall length: 160 mm
- Overall width: 60 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Total lumen output fixture: 2650
- Bulb technology: LED
- Light color: 5000
- Mains power: AC 220-240
- Fixture dimmable: No
- Energy class included light source: B
- IP code: IP65
- Class of protection: Class I – Earthed
- Light source replaceable: No
- Number of light sources: 1

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions & weight

- EAN/UPC – product: 8720169365407
- Net weight: 0.4 kg
- Gross weight: 0.46 kg
- Height: 19.7 cm
- Length: 6.7 cm
- Width: 16.6 cm



Issue date: 2026-04-29
Version: 0.233

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com