



Selectable colour temperatures help you to make the right choice

Enjoy 5 possible light colors in one product. Change the color of your light easily with by switching the button on the product.

High quality light

• Designed for the comfort of your eyes

Choose for a sustainable solution

· Long life bulbs - Lasts up to 15 years

Light beyond illumination

· Instant on

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Instant on

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

- · Intended use: Indoor
- · Lamp shape: Non directional reflector
- · Socket: E27 · Dimmable: Yes · Bulb Finish: Frosted
- · Bulb Material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000
- Ambient temperature range: -20 to +45 °C

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 120 degree(s)
- · Color rendering index (CRI): 80
- Color temperature:
- 2700-3000-4000-5000-6500 K
- · Nominal luminous flux: 950 lm
- · Warm-up time to 60% light: 0.5 s
- · Correlated Color Temperature (Nom): 2700, 3000, 4000, 5000, 6500 K
- · Luminous Flux: 950 lm
- · Luminous Efficacy (rated) (Nom): 105 lm/W

Miscellaneous

- EveComfort: Yes
- · LED Innovations: EyeComfort
- Extra Features: Dimmable

Other characteristics

• EU RoHS compliant: Yes

Packaging information

• EAN: 8721103071071

• EOC: 872110307107100

• Product title: LEDR80 9W E27 DS FR

DIM 1CT/6

Power

• Power Factor (Fraction): 0.9

Power consumption

Power factor: 0.9
Voltage: AC 220-240 V
Wattage equivalent: 60 W
Power Consumption: 9 W

Product dimensions and weight

Overall height: 12.2 mmOverall length: 12.2 mmOverall width: 8 mm

Technical specifications

• Frequency: 50-60

• Dimmable: Only with specific

dimmers
Cap-Base: E27

Packaging dimensions & weight

• EAN/UPC - product: 8721103071071

Net weight: 0.06 kgGross weight: 0.09 kg

Height: 12.7 cmLength: 8 cmWidth: 8 cm



Issue date: 2025-10-08 Version: 0.75 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips