

# PHILIPS

Capsule 1.7W capsule  
G4 2700K NonDim

LED

2700K

210lm

15000h

8721103145451



## Creative innovation to realize LED conversion

Familiar shapes you know and love. They use around 80% less energy than traditional light bulbs and last ten times longer.

### High quality light

- Designed for the comfort of your eyes
- True incandescent-like warm white light

### Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

### The right replacement for your old lamps

- Similar shape and size as standard halogen lamp

# Highlights

**Designed for the comfort of your eyes**



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

**True incandescent-like warm white light**



This bulb has a color temperature of 2700K, providing you with a warm, tranquil atmosphere, perfect for relaxing. This 2700K light is ideal for home lighting design.

**15,000-hour rated average life**



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

**Similar shape and size as standard halogen lamp**



With its beautifully shaped design and familiar dimensions, this is a modern lighting energy-saving, standard, LED lamp. The perfect sustainable replacement for traditional standard halogen lamps.

## Specifications

### Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional capsule
- Socket: G4
- Bulb Finish: Transparent Silicon
- Dimmable: No
- Bulb Material: Transparent

### Design and finishing

- Color: Clear
- Material: Silicone

### Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

**Environmental**

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

**Extra feature/accessory incl.**

- Choose your color: No
- LED integrated: Yes

**Light characteristics**

- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Nominal luminous flux: 210 lm
- Luminous Efficacy (rated) (Nom): 123

**Miscellaneous**

- EyeComfort: Yes
- LED Innovations: EyeComfort

**Packaging information**

- EAN: 8721103145451
- EOC: 872110314545100
- Product title: LED 1.7W G4 WW 12V ND micro SRT6 AU

**Power consumption**

- Power factor: 0.5
- Voltage: AC Electronic 12 V
- Wattage equivalent: 20
- Power: 1.7

**Product dimensions and weight**

- Overall height: 37.5 mm
- Overall length: 37.5 mm
- Overall width: 9.5 mm

**Technical specifications**

- Frequency: -
- Diameter: 9.5 mm
- Bulb technology: LED
- Light color: Warm white light

**The bulb**

- Software upgradable: No

**What's supported**

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

**Packaging dimensions & weight**

- EAN/UPC - product: 8721103145451
- Net weight: 0 kg
- Gross weight: 0.01 kg
- Height: 12.7 cm
- Length: 2.6 cm
- Width: 2.6 cm



Issue date: 2026-05-13  
Version: 0.86

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)