

PHILIPS

Filament Candle Clear
1.9W T25L E14 2700K
NonDim

LED

2700K

260lm

25000h

8721103146908



State-of-the-art LED light bulb for the home

Philips LED light bulbs provide high quality light, with long life, and immediate, significant energy savings.

Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

Create the right light for your home

- A simple LED for everyday use

Highlights

Replaces standard incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional candle
- Socket: E14
- Bulb Finish: Clear
- Dimmable: No
- Bulb Material: Glass

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Choose your color: No
- LED integrated: Yes

Light characteristics

- Beam angle: 300
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Nominal luminous flux: 260 lm
- Luminous Efficacy (rated) (Nom): 136

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Packaging information

- EAN: 8721103146908
- EOC: 872110314690800
- Product title: LED classic 1.9W T25L E14 CL ND RF SRT4

Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage equivalent: 25
- Power: 1.9

Product dimensions and weight

- Overall height: 90 mm
- Overall length: 90 mm
- Overall width: 25 mm

Technical specifications

- Frequency: 50-60
- Diameter: 25 mm
- Bulb technology: LED
- Light color: Warm white light

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions & weight

- EAN/UPC - product: 8721103146908
- Net weight: 0.01 kg
- Gross weight: 0.04 kg
- Height: 12.8 cm
- Length: 0.7 cm
- Width: 6.4 cm



Issue date: 2026-05-13
Version: 0.86

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com