

PHILIPS

Non integrated
compact fluorescent

PL-L

36 W

4 Pin

Cool white

927903408472



Long life and sustainable light output

Philips' Bridge technology gives PLL sticks more light output than traditional PLLs. It also offers 15000hrs of life time, resulting in fewer replacements and lower maintenance costs.

Sustainable choice

- Saves energy

Gives you bright light

- Bridge technology gives PLL lamps more light output

Highlights

Saves energy

Bridge technology

Philips Bridge technology gives PLL lamps more light output than

traditional PLL lamps. It also offers 12000hrs life time means Less replacements, lower maintenance costs.

Specifications

Bulb characteristics

- Socket: 4 Pin
- Dimmable: Yes

Durability

- Nominal lifetime: 15,000

Light characteristics

- Color rendering index (CRI): 82
- Light Color Category: Cool White
- Correlated Color Temperature (Nom): 4100
- Luminous Flux: 2,900
- Luminous Efficacy (rated) (Nom): 81

Power consumption

- Power: 36.0
- Energy Consumption kWh/1000 h: 40

Technical specifications

- Light output: 2,900
- Shape: Tube
- Dimmable: Yes
- Cap-Base: 2G11

Packaging dimensions & weight

- EAN/UPC - product: 8711500706751
- Net weight: 104 g
- Gross weight: 131.01 g
- Height: 2.5 cm
- Length: 42 cm
- Width: 4.5 cm



Issue date: 2026-04-01
Version: 0.571

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com