



# Vibrant experience with extra brightness

Philips Color 80s offer higher light output for extra brightness and better ambiance. They are suitable for applications where light quality is important for a more vibrant experience.

#### **Saves energy**

· Saves energy

## Gives you bright light

· Vibrant experience with extra brightness

# Highlights

Saves energy Bright boost High efficient fluorescent combined with BrightBoost technology for good color rendering and extra brightness

# Specifications

#### **Bulb characteristics**

Socket: G10qDimmable: No

# **Durability**

· Nominal lifetime: 8,000

## **Light characteristics**

· Color rendering index (CRI): 80

· Light Color Category: Cool Daylight

• Correlated Color Temperature (Nom): 6500

· Luminous Flux: 1,250 lm

Luminous Efficacy (rated) (Nom): 57 lm/W

#### **Power consumption**

• Power Consumption: 22.0

• Energy Consumption kWh/1000 h: 24

## **Technical specifications**

• Light output: 1,250 lm

· Shape: Circular fluorescent

Dimmable: YesCap-Base: G10q

#### Packaging dimensions & weight

• EAN/UPC - product: 8711500286673

Net weight: 0.11 kgGross weight: 0.17 kgHeight: 21.4 cm

Length: 3.5 cmWidth: 21.6 cm



Issue date: 2025-11-15 Version: 0.513 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.