




	Good	Good	Good	Better	Better
Series	P100	P100	P100	P1100	P1500
Prefix	P120	P150	P195	P1150	P1511
Pole Desc.	Tapered	Straight	Straight	Tapered	Straight
Base Desc.	Simple	Simple	Simple	Candlestick	Fluted Bottleneck & Square Cover
Height	8', 10', 12', 14'	8', 10'	12', 14', 15', 16', 18', 20'	8'6", 10'6", 12'6"	8', 10', 12'
Diameter	4-3" Tapered	3"	4"	4-3" Tapered	3"
Pole Tenon	3"	3"	4"	3"	3"
Thickness	0.125"	0.125"	0.188"	0.125"	0.125"
Base	11 1/2" dia. x 2 3/8"	9 5/8" dia. x 1 3/8"	11 1/2" dia. x 2 3/8"	11" Round x 30"	8 1/4" sq. x 27 3/8"
Bolt Circle	7 1/2" - 9 1/2"	7"	7 1/2" - 9 1/2"	7"	9-3/8"
Base Cover	Included) 12 1/8" dia. x 3 1/4"	(Included) 10 1/4" dia. x 2 3/4"	-	-	(Included) 9" sq. x 3"
EPA @ 80 MPH	4.11-9.78	2.19-3.19	2.17-6.45	5.55-9.06	6.64-9.99
EPA @ 100 MPH	2.01-6.10	1.07-1.80	0.93-3.88	2.95-5.42	3.72-5.84
EPA @ 110 MPH	-	-	-	-	-
EPA @ 130 MPH	-	-	-	-	-
Outlet Location (Optional)	T	T	T	T, B	T, B
Outlet Options (Optional)	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex
Finish	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Green
Link	https://www.signify.com/api/assets/v1/file/Signify/content/8c-0b0a40ddf0457f9a94a95200908cca/Hadco_P120_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/293dd952d2604d5089dba90b012c95f6/had_1565.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/5a8ed-d676971409398a2a90b012cad80/Hadco_P195_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/7a7fa5bb6d-f741c08088a90b-012c94d2/Hadco_P1150_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/1232f-30d3e9e49babd-8ba90b012c971d/Hadco_P1511_Pole_SpecSheet_Web.pdf

Continued on next page.

Outdoor Aluminum Poles & Brackets



	Better	Better	Better	Best	Best
Series	P1500	P1500	P1500	P1500	P1500
Prefix	P1516	P1521	P1526	P1561	P1566
Pole Desc.	Straight	Tapered	Tapered	Straight Fluted	Straight Fluted
Base Desc.	Fluted Bottleneck & Round Cover	Fluted Bottleneck & Square Cover	Fluted Bottleneck & Round Cover	Fluted Bottleneck & Square Cover	Fluted Bottleneck & Round Cover
Height	8', 10', 12'	8', 10', 12', 14'	8', 10', 12', 14'	8', 10', 12'	8', 10', 12'
Diameter	3"	4-3" Tapered	4-3" Tapered	3"	3"
Pole Tenon	3"	3"	3"	3"	3"
Thickness	0.125"	0.125", 0.188" (14')	0.125", 0.188" (14')	0.125"	0.125"
Base	8 1/4" sq. x 27 3/8"	8 1/4" sq. x 27 3/8"	8 1/4" sq. x 27 3/8"	8 1/4" sq. x 27 3/8"	8 1/4" sq. x 27 3/8"
Bolt Circle	9-3/8"	9-3/8"	9-3/8"	9-3/8"	9-3/8"
Base Cover	(Included) 12 3/4" dia. x 5 1/2"	(Included) 9" sq. x 3"	(Included) 12 3/4" dia. x 5 1/2"	(Included) 9" sq. x 3"	(Included) 12 3/4" dia. x 5 1/2"
EPA @ 80 MPH	6.64-9.99	7.57-10.24	7.57-10.24	6.50-9.77	6.50-9.77
EPA @ 100 MPH	3.72-5.84	4.26-5.78	4.26-5.78	3.65-5.72	3.65-5.72
EPA @ 110 MPH	-	-	-	-	-
EPA @ 130 MPH	-	-	-	-	-
Outlet Location (Optional)	T, B	T, B	T, B	T, B	T, B
Outlet Options (Optional)	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex
Finish	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green
Link	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/805309e-484a747e8a4a1a90b012c9929/had_409.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/42b-93bc978b149ab-93d8a90b012c9ac4/Hadco_P1521_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/be6b42e71731487d-b386a90b012c9be8/Hadco_P1526_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/aeb72e0f324f4219b-92fa90b012c9d14/Hadco_P1561_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/49a2c1e-95a8f46f0adf-ba90b012c9f10/Hadco_P1566_Pole_SpecSheet_Web.pdf

Continued on next page.





Outdoor Aluminum Poles & Brackets



	Better	Better	Best	Better	Better
Series	P1600	P1600	P1700	P1700	P2000
Prefix	P1600	P1610	P1761	P1791	P2025
Pole Desc.	Tapered	Straight	Straight Fluted	Tapered	Tapered
Base Desc.	Pedestal	Pedestal	Fluted Bottleneck on Woodbury Octagon & Square Cover	Fluted Bottleneck on Woodbury Octagon & Square Cover	Fluted
Height	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'
Diameter	4-3" Tapered	4"	4"	4-3" Tapered	5-3" Tapered
Pole Tenon	3"	4"	3"	3"	3"
Thickness	0.125"	0.125"	0.125"	0.125"	0.125", 0.188" (14' and up)
Base	16" dia. x 22"	16" dia. x 22"	10 1/2" sq. x 49"	10 1/2" sq. x 49"	16" Round x 21"
Bolt Circle	8-13"	8-13"	(min) 11 3/8" (max) 12 3/4"	(min) 11 3/8" (max) 12 3/4"	8 x 12"
Base Cover	-	-	(Included) 11 1/2" sq. x 2 1/2"	(Included) 11 1/2" sq. x 2 1/2"	-
EPA @ 80 MPH	5.21-12.53	5.21-12.53	3.10-8.54	3.10-8.54	9.90-14.91
EPA @ 100 MPH	2.64-7.52	2.64-7.52	1.23-4.99	1.23-4.99	5.38-8.83
EPA @ 110 MPH	-	-	-	-	-
EPA @ 130 MPH	-	-	-	-	-
Outlet Location (Optional)	T, B	T, B	T, B	T, B	T, B
Outlet Options (Optional)	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex
Finish	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green
Link	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/ce047b59be-af4a0abeb6a90b-012ca23e/had_412.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/98fdb-f7230a247f6b-5b8a90b012ca412/Hadco_P1610_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/300315e39fe54659bf27a90b012ca7af/Hadco_P1761_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/69dd75d32c554e-279c43a90b012ca928/Hadco_P1791_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/d3d5c86c121e4b-099c91a90b012cb191/had_435.pdf

Continued on next page.




Outdoor Aluminum Poles & Brackets



	Best	Best	Best	Best	Best
Series	P2000	P2000	P2000	P2000	P2000
Prefix	P2060	P2061	P2063	P2065	P2071
Pole Desc.	Straight Fluted	Straight Fluted	Straight Flat Fluted	Straight Flat Fluted	Straight Fluted
Base Desc.	Fluted	Fluted	Fluted	Fluted	Fluted Bottleneck
Height	10', 12', 14'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'
Diameter	4"	4"	4"	5"	4"
Pole Tenon	3"	3"	3"	3"	3"
Thickness	0.125"	0.125"	0.188-0.313"	0.188-0.267"	0.125"
Base	16" Round x 21"	16" Round x 21"	16" Round x 21"	16" Round x 21"	16" Round x 47"
Bolt Circle	12"	8-12"	8-12"	8-12"	8-12"
Base Cover	-	-	-	-	-
EPA @ 80 MPH	4.46-8.23	4.62-11.29	8.84-19.19	11.78-25.34	5.34-12.29
EPA @ 100 MPH	2.24-4.47	1.93-6.17	4.69-11.29	6.34-15.00	2.42-6.74
EPA @ 110 MPH	-	-	-	-	-
EPA @ 130 MPH	-	-	-	-	-
Outlet Location (Optional)	T, B	T, B	T, B	T, B	T, B
Outlet Options (Optional)	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex
Finish	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green
Link	https://www.signify.com/api/assets/v1/file/Signify/content/96f7f-dc20ccd4317ae-c4a90b012cb39b/Hadco_P2060_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/765ff14b-96b8430c899ca-87f012e2960/1_437_anchor_rod_template_t01000735.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/a0006dab55b-94523977da87f012e2d6d/1_438_anchor_rod_template_t01000735.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/159a13f7539e48769df0a87f012e2b98/1_439_ANCHOR_ROD_TEMPLATE_T01000735%5B1%5D.PDF	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/b6bfda5de1e-9491a9b19a87f012e2f87/1_440_anchor_rod_template_t01000735.pdf

Continued on next page.



Outdoor Aluminum Poles & Brackets



	Best	Best	Best	Best	Best
Series	P2100	P2500	P2500	P2500	P2500
Prefix	P2165	P2520	P2525	P2540	P2550
Pole Desc.	Straight Flat Fluted	Tapered	Tapered	Straight Flat Fluted	Straight Flat Fluted
Base Desc.	Fluted	Fluted Bottleneck & Square Cover	Fluted Bottleneck & Fluted Round Cover	Fluted Bottleneck & Square Cover	Fluted Bottleneck & Square Cover
Height	12', 14', 16', 18'	10', 12', 14', 16'	10', 12', 14', 16'	10', 12', 14', 16'	12', 14', 16', 18'
Diameter	5"	5-3" Tapered	5-3" Tapered	4"	5"
Pole Tenon	3"	3"	3"	3"	3"
Thickness	0.188-0.267"	0.125"	0.125"	0.188-0.313"	0.188-0.267"
Base	20 dia. x 25 3/8"	12 3/4 sq. x 43 3/4"	12 3/4 sq. x 43 3/4"	12 3/4 sq. x 43 3/4"	12 3/4 sq. x 43 3/4"
Bolt Circle	8-16"	11-14"	11-14"	11-14"	11-14"
Base Cover	-	(Included) 14" sq. x 9.38"	(Included) 19" dia. x 9 1/4"	(Included) 14" sq. x 9.38"	(Included) 14" sq. x 9.38"
EPA @ 80 MPH	8.78-18.42	12.76-27.80	12.76-27.80	5.54-13.78	10.65-23.42
EPA @ 100 MPH	4.43-10.56	7.46-17.27	7.46-17.27	2.72-8.34	5.99-14.48
EPA @ 110 MPH	-	-	-	-	-
EPA @ 130 MPH	-	-	-	-	-
Outlet Location (Optional)	T, B	T, B	T, B	T, B	T, B
Outlet Options (Optional)	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex
Finish	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green
Link	https://www.signify.com/api/assets/v1/file/Signify/content/f1955b-5840d14ae3a28d-a90b012cbc04/Hadco_P2165_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/1328f69a1a5c4bfd909aa90b012cbff2/had_446.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/4fbd3b-fc506545d-9854ca90b012cc140/Hadco_P2525_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/98d-7d75ce6fa47ab-b386a90b012cc3c5/Hadco_P2540_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/b6d2c5df392f4a39bae-fa90b012cc59c/Hadco_P2550_Pole_SpecSheet_Web.pdf

Continued on next page.



Outdoor Aluminum Poles & Brackets



	Best	Best	Best	Best	Better
Series	P2500	P2500	P2500	P3100	P4000
Prefix	P2555	P2560	P2565	P3165	P4030
Pole Desc.	Straight Flat Fluted	Straight Fluted	Straight Fluted	Straight Flat Fluted	Straight
Base Desc.	Fluted Bottleneck & Fluted Round Cover	Fluted Bottleneck & Square Cover	Fluted Bottleneck & Fluted Round Cover	Fluted Bottleneck with Floral Accent	Bottleneck
Height	12', 14', 16', 18'	10', 12', 14', 16'	10', 12', 14', 16'	12', 14', 16', 18'	12', 14', 16', 18'
Diameter	5"	4"	4"	5"	4"
Pole Tenon	3"	3"	3"	3"	3"
Thickness	0.188-0.267"	0.125"	0.125"	0.188"	0.125"
Base	12 3/4 sq. x 43 3/4"	12 3/4 sq. x 43 3/4"	12 3/4 sq. x 43 3/4"	17" dia. x 29"	15" dia. x 46 1/8"
Bolt Circle	11-14"	11-14"	11-14"	8-13"	8-12"
Base Cover	(Included) 19" dia. x 9 1/4"	(Included) 14" sq. x 9.38"	(Included) 19" dia. x 9 1/4"	-	-
EPA @ 80 MPH	10.65-23.42	5.54-13.78	5.54-13.78	18.99-36.78	8.40-18.69
EPA @ 100 MPH	5.99-14.48	2.72-8.34	2.72-8.34	10.98-22.32	4.83-11.61
EPA @ 110 MPH	-	-	-	-	-
EPA @ 130 MPH	-	-	-	-	-
Outlet Location (Optional)	T, B	T, B	T, B	T, B	T, B
Outlet Options (Optional)	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex
Finish	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green
Link	https://www.signify.com/api/assets/v1/file/Signify/content/698b-0890bab343cb88a-ca90b012cc738/Hadco_P2555_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/c42497b7ad664205be-96a90b012cc9fd/Hadco_P2560_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/99ab-35431cf14946a-6c6a90b012ccb76/Hadco_P2565_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/5b-14831846014109898ba-90b012cd104/Hadco_P3165_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/831b69817e-ba44cebc53a90b-012cd4a1/Hadco_P4030_Pole_SpecSheet_Web.pdf

Continued on next page.




Outdoor Aluminum Poles & Brackets



	Better	Better	Better	Good	Better
Series	P4000	P4100	P4400	P5000	P5000
Prefix	P4031	P4120	P4465	P5020	P5065
Pole Desc.	Straight	Tapered	Straight Flat Fluted	Tapered	Straight Flat Fluted
Base Desc.	Bottleneck	Bottleneck	Fluted Bottleneck	Fluted	Fluted
Height	12', 14', 16', 18'	12', 14', 16', 18'	12', 14', 16', 18'	12', 14', 16', 18'	12', 14', 16', 18'
Diameter	4"	5-3" Tapered	5"	5-3" Tapered	5"
Pole Tenon	4"	3"	3"	3"	3"
Thickness	0.125"	0.125"	0.188-0.267"	0.188"	0.188-0.267"
Base	15" dia. x 46 1/8"	19" dia. x 54 1/2"	15 1/2" dia. x 48"	17" dia. x 21"	17" dia. x 21"
Bolt Circle	8-12"	8-14"	8-12"	8-13"	8-13"
Base Cover	-	-	-	-	-
EPA @ 80 MPH	8.40-18.69	6.72-15.28	10.59.23.29	6.80-13.77	13.99-28.22
EPA @ 100 MPH	4.83-11.61	3.51-9.33	5.95-14.40	3.67-8.12	7.60-16.70
EPA @ 110 MPH	-	-	-	-	-
EPA @ 130 MPH	-	-	-	-	-
Outlet Location (Optional)	T, B	T, B	T, B	T, B	T, B
Outlet Options (Optional)	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex
Finish	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Green	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Gray, Green
Link	https://www.signify.com/api/assets/v1/file/Signify/content/ff4f5f4ba43e451c80a-fa90b012cd6b0/Hadco_P4031_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/dfd68a0a9e-9f40a386b3a90b-012cd7ee/Hadco_P4120_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/9808908c41794ee5907fa90b012ce2a6/Hadco_P4465_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/f5b46b96ec5e40c9af-d8a90b012ce428/Hadco_P5020_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/1ba-1be3e72b94f29b-fafa90b012ce7ea/Hadco_P5065_Pole_SpecSheet_Web.pdf

Continued on next page.

Outdoor Aluminum Poles & Brackets



	Better	Good	Best	Best	Best
Series	P5000	P9000	Washington	Washington	Woodbury/P1700
Prefix	P5092	P9300	306	754	316
Pole Desc.	Tapered Fluted	Straight Flat Fluted	Straight Fluted	Straight Flat Fluted	Tapered
Base Desc.	Fluted	Simple Round	Fluted	Fluted Bottleneck	Fluted Bottleneck on Woodbury Octagon & Square Cover
Height	12', 14', 16'	10', 12', 14', 16'	8', 10', 12', 14', 16'	8', 10', 12', 14', 16'	8', 10', 12', 14'
Diameter	6-4" Tapered	4"	4"	4"	4-3" Tapered
Pole Tenon	3"	3"	3"	3"	3"
Thickness	0.188"	0.188-0.313"	0.125"	0.125"	0.125"
Base	17" dia. x 21"	9" dia.	17" dia x 21-5/8"	17" dia x 18-3/4"	11-1/2" sq. x 12-1/4"
Bolt Circle	8-13"	7"	7"	7"	12-3/8"
Base Cover					
EPA @ 80 MPH	11.61-20.55	7.38-16.65	6.86-19.69	12.35-38.53	10.90-30.02
EPA @ 100 MPH	6.41-12.12	4.03-10.15	-	-	-
EPA @ 110 MPH	-	-	2.42-9.94	5.55-20.07	4.97-15.56
EPA @ 130 MPH	-	-	1.07-8.47	-	3.59-10.13
Outlet Location (Optional)	T, B	T	T, B	T, B	T, B
Outlet Options (Optional)	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex	Standard Duplex GFI Duplex
Finish	Black, White, Verde, Bronze, Gray, Green	Black, White, Verde, Bronze, Green	Standard Hanover Finishes (see reference sheet)	Standard Hanover Finishes (see reference sheet)	Standard Hanover Finishes (see reference sheet)
Link	https://www.signify.com/api/assets/v1/file/Signify/content/2d98ed83a3fc439d89f2a90b012cea5e/Hadco_P5092_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/9c11c064627f40f8a04ca90b012cf5ea/Hadco_P9300_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/30a528ab1d6d4831b653a90c007a8147/Hadco_306_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/88decdf8bd1549b5ae8ba90c007a91d0/Hadco_754_Pole_SpecSheet_Web.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/69dd75d32c554e279c43a90b012ca928/Hadco_P1791_Pole_SpecSheet_Web.pdf



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.