





		Specification-grade	
		Best	Best
		Calculite 2"/3" cylinder	Calculite 4"/6" cylinder
Trims	Sizes	○ 2" & 3" □ 3"	○ 4" & 6"
	Styles	Downlight, Wall Wash, Adjustable Accent, Direct/Indirect, Up/Down	Downlight (N, M, W), Open Wall Wash, Double Wall Wash
	Beams	2": 62° 3": 33°, 55°, 62°	40° to 76° (6 beams)
	Reflectors	Specular clear, Comfort clear, Comfort clear diffuse, Champagne bronze, Black	Specular clear, Comfort clear, Comfort clear diffuse, Champagne bronze, Black
	Flanges	<b>Cylinder finishes:</b> Aluminum, White & Black, Plus any RAL color	<b>Cylinder finishes:</b> Aluminum, White & Black
Performance	Applications	Commercial, Architectural & High-end residential	
	Lumens	2": 700lm to 1000lm 3": 1000lm to 3000lm	500, 1000, 1500, 2000, 2500, 3000, 3500, 4800, 6000
	Watts	9-30W	6-57W
	Efficacy	up to 95lm/W	up to 115lm/W
	CCTs (K)	2700, 3000, 3500, 4000 Dim-to-Warm	2700, 3000, 3500, 4000, 5000 Dim-to-Warm, Tunable White
	CRIs	90 	90 
	Lifetime	60,000hrs (L90)	60,000hrs (L90)
Technology	Dimming	0-10V, Lutron, ELV	0-10V, EldoLED, DMX, DALI, Lutron, ELV
	Emergency	-	-
	Controls	2"/3" Interact (remote via SBA)	4"/6" Interact (integral RA, remote via SBA)
	Accessories	Surface mount, Pendant with stem kit, Pendant with cable kit, Wall mount	Surface Mount, Wall mount, Pendant with stem kit, Pendant with cable kit
	Installations	New Construction, Wet locations	New Construction, Wet locations
	Labels	cULus listed, CCEA, IC & Title 24 rated, RoHS, ENERGY STAR	cULus listed, CCEA, IC & Title 24 rated, RoHS, ENERGY STAR
	Warranty	5-year limited	5-year limited