

# LIGHTOLIER

by 

## Downlighting

### Recessed downlights

### Product Selection Guide

Reference	
★ 3	High applicability
★ 2	Medium applicability
★ 1	Low applicability
Blank	Non-applicable



		Good		Better		Best	
		CorePro	Lytecaster	EasyLyte	Lyteprofile	Calculite	
Applicability	Retail	★ 3	★ 2	★ 3	★ 2	★ 3	
	Hospitality	★ 2	★ 3	★ 3	★ 3	★ 3	
	Office	★ 2	★ 2	★ 3	★ 3	★ 3	
	Education	★ 3	★ 3	★ 3	★ 3	★ 2	
	Residential	★ 3	★ 3	★ 2	★ 2	★ 2	
Features / Performance	Sizes	4", 5", 6"	3", 4", 5", 6"	4", 6"	3", 4", 6"	2", 3", 4", 6", 7"	
	Shape	Round	Round, Square	Round	Round, Square	Round, Square	
	Lumen Range	750-1250	650-2000	500-3500	500-3500	500-6000	
	Efficacy	up to 89lm/W	up to 90lm/W	up to 100lm/W	up to 100lm/W	up to 115lm/W	
	Reflector Options	2	2	3	3	4	
	Trim Direct Cutoff	-	-	70°	60°	50°	
	Trim Reflected Cutoff	-	-	-	-	45°	
	Accent Adjustment	-	30°	-	40°	45°	
	CRI	80-90	80-90	80-90	80-90	90	
	SDCM	3	3	3	3	2	
	Emergency	-	-	Yes	Yes	Yes	
	Life (@60K)	50,000hrs	50,000hrs	50,000hrs	50,000hrs	60,000hrs	
	Controls	Tunable White	-	-	-	Yes	Yes
Dim to Warm		-	-	-	Yes	Yes	
Interact		Yes	Yes	Yes	Yes	Yes	
IntelliHue		-	-	-	-	Yes	
POE		-	-	Yes	Yes	Yes	



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation  
200 Franklin Square Drive,  
Somerset, NJ 08873  
Telephone 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.