

LIGHTOLIER

by 

Downlighting

Surface downlights

Product Selection Guide



		Budget-grade	Value-grade
		Good	Better
		Surface-mount downlight	SlimSurface
Trims	Styles	○ 5", 7"	○ 5", 7", 10" □ 4", 6"
	Flanges	Matches Aperture	Matches Aperture
	Reflectors	White	Aluminum White & Black Metal (10" only)
	Types	Downlight	Downlight
	Beams	Wide	Wide
Performance	Applications	-	-
	Lumens	700, 1000	650, 1000, 2200
	Watts	10-15W	9-28W
	Efficacy	up to 69lm/W	up to 94lm/W
	CCTs (K)	3000	2700, 3000, 3500, 4000
	CRIs	90	80, 90
	Lifetime	50,000hrs (L70)	50,000hrs (L70)
Technology	Dimming	TRIAC	0-10V, ELV, TRIAC
	Emergency	-	-
	Accessories	-	-
	Installations	New Construction Remodeler Wet locations	Wet locations Damp locations (10")
	Labels	cETLus listed IC & Title 24 rated, RoHS, ENERGY STAR	cULus listed, Title 24 rated, RoHS, ENERGY STAR
	Warranty	5-year limited	5-year limited



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.