

LIGHTOLIER

by  Signify

Track lighting

Track & Recessed

Product Selection Guide



		Specification-grade				
		Best	Best	Best	Best	Best
		Alcyon vertical	Alcyon recessed multiple	Alcyon horizontal	OmniSpot	OmniSpot recessed multiple
Features	Finishes	Aluminum White & Black	White & Black	Aluminum White & Black	Aluminum White & Black	Aluminum White & Black
	Adapters	Lightolier, Prospec, Juno, Halo	-	-	Lightolier, Prospec, Juno, Halo, Capri, Global	-
	Optics	Interchangeable	Interchangeable	Interchangeable	Interchangeable	Interchangeable
	Reflectors	Narrow Spot, Spot, Narrow Flood, Flood	Narrow Spot, Spot, Narrow Flood, Flood	Spot, Narrow Flood, Flood	Narrow Spot, Spot, Narrow Flood, Flood	Narrow Spot, Spot, Narrow Flood, Flood
	Beams	10° to 36° (4 beams)	10° to 36° (4 beams)	13° to 28° (3 beams)	11° to 36° (4 beams)	11° to 36° (4 beams)
Performance	Applications	Commercial, Architectural, Hospitality, Retail & High-end residential				
	Lumens	600, 1000, 2000, 3000	600, 1300, 2000	1100	600, 1000, 2000	600, 1000
	Watts	10-34W	10-34W	15W	6-25W	6-12W
	Efficacy	up to 93lm/W	up to 60lm/W	up to 78lm/W	up to 108lm/W	up to 83lm/W
	Technology	CrispWhite	-	CrispWhite	CrispWhite PremiumColor	CrispWhite
	CCTs (K)	2700, 3000, 4000	2700, 3000, 4000	2700, 3000, 3500, 4000	2700, 3000, 3500, 4000	2700, 3000, 3500, 4000
	CRIs	80, 90	80, 85	80, 90	80, 90	80, 90
	CBCP	up to 46,000cd	up to 14,400cd	up to 11,700cd	up to 30,000cd	up to 8,700cd
	Lifetime	50,000hrs (L70)	50,000hrs (L70)	50,000hrs (L70)	50,000hrs (L70)	50,000hrs (L70)
Technology	Dimming	ELV	0-10V	ELV	ELV	0-10V
	Mounting	Track	Recessed	Track	Track	Recessed
	Accessories	Accessory holder, Snoot, Diffusion filters/films, Hex cell louver				
	Installations	New construction				
	Labels	cULus listed, ENERGY STAR	cULus listed, ENERGY STAR	cULus listed, ENERGY STAR	cULus listed, ENERGY STAR	cULus listed, ENERGY STAR
	Warranty	5-year limited	5-year limited	5-year limited	5-year limited	5-year limited

Continued on next page.

Track lighting Track & Recessed



		Performance-grade		
		Better	Better	Better
		SpotLED	BoldFlood	LightFlood
Features	Finishes	Aluminum White & Black	Aluminum White & Black	Aluminum White & Black
	Adapters	Lightolier, Halo, Juno, GES, GTek, HTek	Lightolier, Halo, Juno	-
	Optics	Integrated	Integrated	Integrated
	Reflectors	Spot, Narrow Flood, Flood	Flood	Spot, Narrow Flood, Flood
	Beams	8° to 40° (3 beams)	95° W x 90° L	100°
Performance	Applications	Commercial, Architectural, Hospitality, Retail & High-end residential		
	Lumens	600, 1000, 2000, 3000	2000, 4000,	2000, 4000
	Watts	10-39W	23-41W	23W
	Efficacy	up to 78lm/W	up to 100lm/W	up to 100lm/W
	Technology	-	-	CrispWhite
	CCTs (K)	2700, 3000, 4000	2700, 3000, 3500, 4000	3000, 4000
	CRIs	80, 85	90	80
	CBCP	up to 70,000cd	up to 1,808cd	up to 900cd
	Lifetime	54,000hrs (L70)	50,000hrs (L70)	50,000hrs (L70)
Technology	Dimming	ELV	ELV	ELV, TRIAC
	Mounting	Track	Track	Track
	Accessories	Accessory holder, Snoot, Diffusion filters, Color filters, Hex cell louver	Louver, Visor	-
	Installations	New construction		
	Labels	cULus listed, ENERGY STAR	cULus listed, ENERGY STAR	cULus listed
	Warranty	5-year limited	5-year limited	5-year limited

Continued on next page.

Track lighting Track & Recessed



		Value-grade		
		Good	Good	Good
		Track Head	CorePro LED	Gimbal LED
Features	Finishes	Aluminum, White & Black	Aluminum, White & Black	Aluminum, White & Black
	Adapters	Lightolier, Juno	Lightolier, Halo, Juno	-
	Optics	Integrated	Integrated	Interchangeable
	Reflectors	Narrow Spot, Spot, Narrow Flood, Flood	Narrow Spot, Wide Flood	(determined by PAR30/38 lamping)
	Beams	15° to 36° (4 beams)	23° to 35° (2 beams)	
Performance	Applications	Commercial, Architectural, Hospitality, Retail & High-end residential		
	Lumens	600, 1000	600, 1000, 2000	(determined by PAR30/38)
	Watts	6-12W	6-12W	
	Efficacy	up to 90lm/W	up to 107lm/W	
	Technology	-	CrispWhite PremiumColor	
	CCTs (K)	3000	2700, 3000	
	CRIs	90	80, 90	
	CBCP	up to 12,300cd	up to 2,900cd	
	Lifetime	40,000 to 60,000hrs (L70)	50,000hrs (L70)	
Technology	Dimming	0-10V	ELV	-
	Mounting	Track	Track	Track
	Accessories	Accessory holder, Snoot, Diffusion filters, Color filters, Hex cell louver	-	-
	Installations	New construction		
	Labels	cULus listed, ENERGY STAR	cULus listed, ENERGY STAR	cULus listed
	Warranty	5-year limited	5-year limited	5-year limited



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.