

Powerful portfolio of all-in-one selectable products to impress your toughest customer with CCT & lumen select on the fly.



Reference	
3	High applicability
2	Medium applicability
1	Low applicability
Blank	Non-applicable

	Budget-grade	Budget-grade	Budget-grade	Budget-grade	Budget-grade	Budget-grade	Value-grade	
	Good	Good	Good	Good	Good	Good	Good	
	Commercial Retrofit Downlight DualSelect	Retrofit Downlight	Flat Downlight Select	Mini Downlight	Mini Gimbal	Surface Mount	SlimSurface LED	
Applicability	Retail	3	1	1	2	2	3	
	Hospitality	3	1	1	2	2	3	
	Office	3	1	1	1	1	3	
	Education	3	1	1	1	1	3	
	Residential	2	3	3	3	3	3	
Features / Performance	Sizes	4", 6", 8", 10"	4", 5/6"	3", 4", 5", 6", 8"	3", 4", 6"	3", 4", 6"	5", 7", 9" 11", 14"	
	Shape	Round	Round	Round & Square	Round	Round	Round	
	Color Temperature	3000K, 3500K, 4000K (CCT Field Selectable)	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, and 5000K)	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, and 5000K)	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, and 5000K)	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, and 5000K)	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, and 5000K)	2700K, 3000K, 3500K, 4000K
	Lumen Range	500-3000lm (Lumen Field Selectable)	700lm, 900lm	370-1300lm (Lumen Field Selectable)	(375-1185lm ) (Lumen Field Selectable)	375-1185lm (Lumen Field Selectable)	700-2000lm (Lumen Field Selectable)	650lm, 1000lm, 2200lm
	Efficacy	up to 93lm/W	up to 78lm/W	up to 70lm/W	up to 70lm/W	up to 72lm/W	up to 74lm/W	up to 95lm/W
	Reflector Option	-	-	-	-	-	-	-
	Trim Direct Cutoff	-	-	-	-	-	-	-
	Trim Reflected Cutoff	-	-	-	-	-	-	-
	Accent Adjustment	-	-	-	-	-	-	-
	CRI	90	90	90	90	90	90	80/90
	SDCM	3	3	3	3	3	3	3
	Emergency	-	-	-	-	-	-	-
	Life	50,000hrs	50,000hrs	50,000hrs	50,000hrs	50,000hrs	50,000hrs	50,000hrs
Controls	Tunable White	-	-	-	-	-	-	
	Dimming	0-10V dim	ELV/TRIAC	ELV/Triac & 0-10V dim	ELV/Triac & 0-10V dim	ELV/Triac & 0-10V dim	ELV/TRIAC/0-10V	
	Interact	-	-	-	-	-	-	
	Intellihue	-	-	-	-	-	-	
	POE	-	-	-	-	-	-	
	Link							