

LIGHTOLIER

Reference	
★ 3	High applicability
★ 2	Medium applicability
★ 1	Low applicability
Blank	Non-applicable



		Better			Best
		LyteCaster	EasyLyte	LyteProfile	Calculite
Applicability	Retail	★ 2 ★	3 ★	★	3
	Hospitality	★ 3 ★	3 ★	★	3
	Office	★ 2 ★	3 ★	★	3
	Education	★ 3 ★	3 ★	★	2
	Residential	★ 3 ★	2 ★	★	2
Features / Performance	Sizes	3", 4", 5", 6"	4", 6"	3", 4", 6"	2", 3", 4", 6", 7"
	Shape	Round, Square	Round	Round, Square	Round, Square
	Lumen Range	650-2000	500-3500	500-3500	500-6000
	Efficacy	up to 90lm/W	up to 100lm/W	up to 100lm/W	up to 115lm/W
	Reflector Options	2	3	3	4
	Trim Direct Cutoff	-	70°	60°	50°
	Trim Reflected Cutoff	-	-	-	45°
	Accent Adjustment	30°	-	40°	45°
	CRI	80-90	80-90	80-90	90
	SDCM	3	3	3	2
	Emergency	-	Yes	Yes	Yes
	Life (@60K)	50,000hrs	50,000hrs	50,000hrs	60,000hrs
Controls	Tunable White	-	-	Yes	Yes
	Dim to Warm	-	-	Yes	Yes
	Interact	Yes	Yes	Yes	Yes
	IntelliHue	-	-	-	Yes
	POE	-	Yes	Yes	Yes



a @ignify business

© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 800-555-0050

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.