



Reference	
★ 3	High applicability
★ 2	Medium applicability
★ 1	Low applicability
Blank	Non-applicable



		Good	Better		Best
		★ LyteCaster	★ EasyLyte	LyteProfile	Calculite
Applicability	Retail	★ 2	★ 3	★ 2	★ 3
	Hospitality	★ 3	★ 3	★ 3	★ 3
	Office	★ 2	★ 3	★ 3	★ 3
	Education	★ 3	★ 3	★ 3	★ 2
	Residential	★ 3	★ 2	★ 2	★ 2
Features / Performance	Retrofit Ready	Remodeler frames available	Flex	Flex	Flex
	Sizes	3", 4", 5", 6"	4", 6"	3", 4", 6"	2", 3", 4", 6", 7"
	Shape	Round, Square	Round	Round, Square	Round, Square
	Lumen Range	650-2000	500-3500	500-5000	500-6000
	Style	Downlight, Accent, Gimbal	Downlight	Downlight, Wall Wash, Accent	Downlight, Wall Wash, Accent
	Efficacy	up to 90lm/W	up to 100lm/W	up to 100lm/W	up to 115lm/W
	Reflector Options	2	3	3	4
	Trim Direct Cutoff	70°	70°	60°	50°
	Trim Reflected Cutoff	70°	70°	60°	45°
	Accent Adjustment	30°	-	40°	45°
	CRI	90	90	90	90
	SDCM	3	3	2	2
	Emergency	-	Yes	Yes	Yes
	Life	L70 @ 50k hrs 🌈	L70 @ 50k hrs 🌈	L80 @ 60k hrs 🌈	L90 @ 60k hrs 🌈
Controls	Tunable White	-	-	Yes	Yes
	Dimming	-	0-10v, phase-cut	0-10v, phase-cut	0-10v (1%, 0.1%), Lutron, DALI, DMX, phase-cut
	Dim to Warm	-	-	Yes	Yes
	Interact	Yes	Yes	Yes	Yes