

ADVANCE

by  Signify

Ballasts

Cross Reference Guide

Robertson to Advance

Competitor Name	Competitor Part Number	Advance	Notes	Ballast Type	Ballast Family
Robertson	ISS232T8MVW	IOPA-2P32-N		Electronic Fluorescent	Optanium
Robertson	PAT128T5MVT	ICN-2S28-T	Or ICN-2S28-N (9.5" x 1.3" x 1.0")	Electronic Fluorescent	Centium
Robertson	PAT154T5MVT	ICN-2S54-T	Or ICN-2S54-N (9.5" x 1.3" x 1.0")	Electronic Fluorescent	Centium
Robertson	PAT228T5MVT	ICN-2S28-T	Or ICN-2S28-N (9.5" x 1.3" x 1.0")	Electronic Fluorescent	Centium
Robertson	RED132T8120	IOP-1PSP32-N		Electronic Fluorescent	Optanium
Robertson	RED139TT120	ICN-2S24-N		Electronic Fluorescent	Centium
Robertson	RED140TT120	ICN-1TTP40-SC		Electronic Fluorescent	Centium
Robertson	RED150TT120	ICN-2S54-N		Electronic Fluorescent	Centium
Robertson	REH239TT120	ICN-2S24-N		Electronic Fluorescent	Centium
Robertson	REI132T8120	ICN-1P32-N		Electronic Fluorescent	Centium
Robertson	REI132T8277	ICN-1P32-N		Electronic Fluorescent	Centium
Robertson	REI232T8120	ICN-2P32-N		Electronic Fluorescent	Centium
Robertson	REI232T8277	ICN-2P32-N		Electronic Fluorescent	Centium
Robertson	REI259T8120	IOP-2P59-N		Electronic Fluorescent	Optanium
Robertson	REI259T8277	IOP-2P59-N		Electronic Fluorescent	Optanium
Robertson	REI332T8120	ICN-3P32-N		Electronic Fluorescent	Centium
Robertson	REI332T8277	ICN-3P32-N		Electronic Fluorescent	Centium
Robertson	REI432T8120	ICN-4P32-N		Electronic Fluorescent	Centium
Robertson	REI432T8277	ICN-4P32-N		Electronic Fluorescent	Centium
Robertson	RER1LT8120	IOP-1PSP32-N		Electronic Fluorescent	Optanium
Robertson	RER1LT8120H	IOPA-1P32-HL-N	Robertson ballast is Rapid Start; Advance offering is Instant Start, Robertson ballast is <10% THD; Advance offering is <20% THD	Electronic Fluorescent	Optanium
Robertson	RER1LT8120R	IOP-1S32-LW-SC		Electronic Fluorescent	Optanium
Robertson	RER1LT8230	ICN-1P32-N	Robertson ballast is Rapid Start; Advance offering is Instant Start	Electronic Fluorescent	Centium
Robertson	RER1LT8277	IOP-1PSP32-N		Electronic Fluorescent	Optanium
Robertson	RER1LT8277H	IOPA-1P32-HL-N	Robertson ballast is Rapid Start; Advance offering is Instant Start, Robertson ballast is <10% THD; Advance offering is <20% THD	Electronic Fluorescent	Optanium
Robertson	RER1LT8277R	IOP-1S32-LW-SC		Electronic Fluorescent	Optanium
Robertson	RER1LT8347	GOP-2PSP32-SC		Electronic Fluorescent	Optanium

Cross Reference Guide Robertson to Advance

Competitor Name	Competitor Part Number	Advance	Notes	Ballast Type	Ballast Family
Robertson	RER2LT8120	IOP-2P59-N		Electronic Fluorescent	Optanium
Robertson	RER2LT8120H	IOPA-2P32-HL-N	Robertson ballast is Rapid Start; Advance offering is Instant Start, Robertson ballast is <10% THD; Advance offering is <20% THD	Electronic Fluorescent	Optanium
Robertson	RER2LT8120R	IOP-2PSP32-LW-N		Electronic Fluorescent	Optanium
Robertson	RER2LT8230	ICN-2P32-N	Robertson ballast is Rapid Start; Advance offering is Instant Start	Electronic Fluorescent	Centium
Robertson	RER2LT8230R	IOP-2PSP32-LW-N		Electronic Fluorescent	Optanium
Robertson	RER2LT8277	IOP-2P59-N		Electronic Fluorescent	Optanium
Robertson	RER2LT8277H	IOPA-2P32-HL-N	Robertson ballast is Rapid Start; Advance offering is Instant Start, Robertson ballast is <10% THD; Advance offering is <20% THD	Electronic Fluorescent	Optanium
Robertson	RER2LT8277R	IOP-2PSP32-LW-N		Electronic Fluorescent	Optanium
Robertson	RER2LT8347	GOP-2PSP32-SC		Electronic Fluorescent	Optanium
Robertson	RER2LT8347R	GOPA-2P32-LW-SC		Electronic Fluorescent	Optanium
Robertson	RER332T8120	IOP-3PSP32-SC		Electronic Fluorescent	Optanium
Robertson	RER332T8277	IOP-3PSP32-SC		Electronic Fluorescent	Optanium
Robertson	RER432T8120	IOP-4PSP32-SC		Electronic Fluorescent	Optanium
Robertson	RER432T8120R	IOP-4PSP32-LW-SC		Electronic Fluorescent	Optanium
Robertson	RER432T8230	ICN-4P32-N	Robertson ballast is Rapid Start; Advance offering is Instant Start	Electronic Fluorescent	Centium
Robertson	RER432T8277	IOP-4PSP32-SC		Electronic Fluorescent	Optanium
Robertson	SP258	LC-25-TP		Magnetic Fluorescent	Standard



© 2019 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

PAd_1436CR_CRG_Robertson_ODLI20150513_001-UPD 09/19 www.signify.com/advance

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008