



	Best	Best	Better
	PureForm Bollard	Full Cutoff Bollard	Louver Bollard BR830
Prefix	PBL	BR840	BRM83
Lumen Output Range	500 - 4200	986-2,000	1,226
Efficacy	72-100	112-128	32
Distribution	Type 3, 5	Type 3, 5	
Color Temperature	2700*, 3000, 4000, 5000, Amber*	2700*, 3000, 4000, 5000, Amber*	3000, 4000, 5000
Height	3-5'	-	-
Emergency (0°C to 40°C)	Yes	-	-
Field Adjustable Wattage Selector (FAWS)	Yes	No	No
Auto Profile Dimming	Yes	No	No
Motion Response	Yes	Yes	Yes
SiteWise	Yes	No	Yes
Wireless Controls	Yes	No	No
Photocell	Button	Button	-
Additional Options		-	-
IP Rating	IP65	IP66	-
DLC Listing	Standard	-	-
Certifications	UL	UL	UL
Lifetime	L70-100,000h	L70-100,000h	L70-100,000h
Limited Warranty	5 years	5 years	5 years
Link	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/b76f0eb-6ca1d4ccb0ea882008939ca/PBL_PureForm_bollard_1220.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/7ec8ffd4af-974d95ae4ba8f600b3d447/led_bollard_br840_series.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/4229953a8a-f94adcb301a9690079dec8/led_bollard_brm830_series.pdf

