



	Best	Best	Best	Better
	ClearScape Small	ClearScape Medium	Designer Floodlight LED	PowerForm LED High output floodlight
Prefix	CSFS	CSFM	DFL7	PFF
Lumen Output Range	2,050-10,700	9,100-21,200	3,900-10,300	22,200-101,400
Efficacy	95-111	100-119	93-118	94-118
Distribution	Spot, Rectangular Spot, Assymmetric, Rectangular Narrow Flood, Rectangular Medium Flood	Spot, Rectangular Spot, Assymmetric, Rectangular Narrow Flood, Rectangular Medium Flood	Spot, Rectangular Spot, Assymmetric, Rectangular Narrow Flood, Rectangular Medium Flood	Spot, Assymmetric, Rectangular Medium Flood, Airport Apron Flood
Color Temperature	3000, 4000, 5700	3000, 4000, 5700	3000, 4000, 5700	4000
Mounting Height Range	-	-	-	-
0 Uplight	No	No	No	No
Field Adjustable Wattage Selector (FAWS)	No	No	No	No
Dual Circuit Control	No	No	No	No
Auto Profile Dimming	No	No	No	Yes
Motion Response	Yes	Yes	No	Yes
SiteWise	Yes	Yes	No	Yes
Wireless Controls	No	No	No	Yes - order separately
Service Tag	-	-	-	-

Continued on next page.

# Outdoor Floodlights

	Best	Best	Best	Better
	ClearScape Small	ClearScape Medium	Designer Floodlight LED	PowerForm LED High output floodlight
Prefix	CSFS	CSFM	DFL7	PFF
Photocell	Button, TLR, TLRPC	Button, TLR, TLRPC	Button	Button, TLRD5, TLRD7, TLRPC
Additional Options	-	-	-	Custom color
Mounting	Slip Fitter, Yoke Mount	Slip Fitter	Ground/Floor, Wall	Slip Fitter, Yoke Mount
Finish	Textured: Bronze, White, Black, Medium Grey, Dark Grey	Textured: Bronze, White, Black, Medium Grey, Dark Grey	Bronze, White, Black, Medium Grey, Dark Grey	Bronze, White, Black, Medium Grey, Dark Grey
IP Rating	IP66	IP66	IP66	IP66
Vibration	3G	3G	-	3G
DLC Listing	-	-	-	-
Certifications	UL,cUL	UL,cUL	cULus	cULus
Lifetime	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h
Limited Warranty	5 years	5 years	5 years	5 years
Link	<a href="https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/a56b2eb3908f4ab-cb18ca87f0122ce1e/ClearScape_CSFS.pdf">https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/a56b2eb3908f4ab-cb18ca87f0122ce1e/ClearScape_CSFS.pdf</a>	<a href="https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/481391c8722c4ed-29d27a87f0122c898/ClearScape_CSFM.pdf">https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/481391c8722c4ed-29d27a87f0122c898/ClearScape_CSFM.pdf</a>	<a href="https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/de26a9057ca3457888b3a-c0900a288ce/Designer_Flood_DFL7_DFC7.pdf">https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/de26a9057ca3457888b3a-c0900a288ce/Designer_Flood_DFL7_DFC7.pdf</a>	<a href="https://www.signify.com/api/assets/v1/file/Signify/content/e5712969b1bf4f-c682bface200e9d2e1/PowerForm_flood_PFF_Gen2.pdf">https://www.signify.com/api/assets/v1/file/Signify/content/e5712969b1bf4f-c682bface200e9d2e1/PowerForm_flood_PFF_Gen2.pdf</a>



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation  
200 Franklin Square Drive,  
Somerset, NJ 08873  
Telephone 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.