



	Best PureForm Area Medium Comfort	Best PureForm Area Medium Precision	Best PureForm Area Large Precision
Prefix	P26	P26	P34
Lumen Output Range	2,200-9,100	6,700-28,900	22,200-50,000
Efficacy	92-105	98-152	87-133
Distribution	Type 2, 3, 5	Type 2, 3, 4, 5, 5W, AFR, BLC	Type 2, 3, 4, 5, 5W, AFR, BLC
Color Temperature	2700, 3000, 4000, 5000, Amber	2700*, 3000, 4000, 5000, Amber	2700*, 3000, 4000, 5000, Amber
Mounting Height Range	10'-25'	15-35'	30-50'
0 Uplight	Yes	Yes	Yes
Field Adjustable Wattage Selector (FAWS)	Yes	Yes	Yes
Dual Circuit Control	-	Yes	Yes
Auto Profile Dimming	Yes	Yes	Yes
Motion Response	Yes	Yes	Yes
SiteWise	Yes	Yes	Yes
Wireless Controls	Yes	Yes	Yes
Service Tag	-	-	-
Photocell	Button, TLRD5, TLRD7	Button, TLRD5, TLRD7	Button, TLRD5, TLRD7
Additional Options	-	-	-
Mounting	Standard Arm, Adjustable Slipfitter, Wall Mount, Retrofit Arm Mount	Standard Arm, Adjustable Slipfitter, Wall Mount, Retrofit Arm Mount	Standard Arm, Adjustable Slipfitter, Wall Mount, Retrofit Arm Mount
Finish	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey
IP Rating	IP65	IP66	IP65
Vibration	3G	3G	1.5G
DLC Listing	Standard	Premium	Premium
Certifications	-	-	-
Lifetime	-	-	-
Limited Warranty	5 years	5 years	5 years
Link	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/82ff82a-4581646419f20aa4600b888f2/P26_PureForm_area_medium_comfort.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/339d-b76447ef4b83bc3aaa4600b8903f/P26_PureForm_area_medium.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/f211c135cad4419979baa4600b8818a/P34_PureForm_area_large.pdf

Continued on next page.

Outdoor Site & Area lighting



	Better	Better	Better	Better
	EcoForm Area Small	EcoForm Area Large	PowerForm Site and Area	Gullwing Small LED
Prefix	ECF-S	ECF-L	PFAS	GL13
Lumen Output Range	6,715-26,427	27,000-42,006	21,635-95,741	6652-9,870
Efficacy	113-133	112-128	87-119	90-97
Distribution	Type 2, 3, 4, 5, 5W, AFR	Type 2, 3, 4, 5, 5W, AFR	Type 2, 3, 4, 5W, AFR	Type 2, 3, 4, 5
Color Temperature	3000, 4000, 5000	3000, 4000, 5000	3000, 4000	3000, 4000, 5700
Mounting Height Range	8-40'	8-40'	8-40'	?
0 Uplight	Yes	Yes	Yes	Yes
Field Adjustable Wattage Selector (FAWS)	Yes	Yes	No	No
Dual Circuit Control	Yes	Yes	Yes	-
Auto Profile Dimming	Yes	Yes	Yes	Yes
Motion Response	Yes	Yes	Yes	Yes
SiteWise	Yes	Yes	Yes	Yes
Wireless Controls	Yes	Yes	Yes	-
Service Tag	-	-	-	-
Photocell	Button, TLRD5, TLRD7, TLRPC	Button, TLRD5,T LRD7, TLRPC	Button, TLRD5, TLRD7, TLRPC	-
Additional Options	-	-	-	-
Mounting	Standard Arm, Adjustable Slipfitter, Wall Mount, Retrofit Arm Mount	Standard Arm, Adjustable Slipfitter, Wall Mount, Retrofit Arm Mount	Arm Mount, Slip Fitter Mount	Single, Wall Mount Recessed, Wall Mount J-Box
Finish	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Natural Aluminium
IP Rating	IP66	IP66	IP66	IP65
Vibration	3G	3G	1.5G	-
DLC Listing	Premium	Premium	Standard	-
Certifications	UL/cUL	UL/cUL	cULus	UL/cUL
Lifetime	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h
Limited Warranty	5 years	5 years	5 years	5 years
Link	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/40dda82b-4c5e4a728813a87f01235626/ECF-S_EcoForm_area_small.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/c89f9501dc-ca4479b5dea87f01234d44/ECF-L_EcoForm_area_large.pdf	https://www.signify.com/api/assets/v1/file/Signify/content/d793418bbf3f4b-85902cacdf006b91aa/PFAS_PowerForm_area_Gen2.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/bbdab7b4f-2be4aaaac74a87f0123a1a8/Gullwing_GL13_LED.pdf

Continued on next page.

Outdoor Site & Area lighting



	Better	Better	Better
	Gullwing Large LED	Form Ten Square Area LED	Form Ten Round Area LED
Prefix	GL18	-	-
Lumen Output Range	5,710-29,497	5,203- 21,754	5,141-21,852
Efficacy	87-124	93-113	97-113
Distribution	Type 2, 3, 4, 5	Type 2, 3, 4, 5	Type 2, 3, 4, 5
Color Temperature	3000, 4000, 5700	3000, 4000, 5700	3000, 4000, 5700
Mounting Height Range	8-40'	-	-
0 Uplight	Yes	Yes	Yes
Field Adjustable Wattage Selector (FAWS)	No	No	No
Dual Circuit Control	Yes	-	-
Auto Profile Dimming	Yes	No	-
Motion Response	Yes	No	-
SiteWise	Yes	No	-
Wireless Controls	Yes	No	-
Service Tag	-	-	-
Photocell	-	TLRD5, TLRPC	TLRD5, TLRPC
Additional Options	-	-	-
Mounting	Pole Mounted	Arm mounts, Wall mount, Mast Arm Fitter	Arm mounts, Wall mount, Mast Arm Fitter
Finish	Bronze, Black, White, Natural Aluminium	Bronze Anodized, Black Anodized, Natural Anodized, Bronze, White, Medium Grey	Bronze Anodized, Black Anodized, Natural Anodized, Bronze, White, Medium Grey
IP Rating	IP66	-	-
Vibration	-	-	-
DLC Listing	-	-	-
Certifications	UL/cUL	UL/cUL	UL/cUL
Lifetime	L70-100,000h	L70-100,000h	L70-100,000h
Limited Warranty	5 years	5 years	5 years
Link	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/9cd-4b441ebff484d934baa8d00d01747/Gullwing_GL18_LED_1020.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/70f5a1de-aea74fcb8264ab7900e14cc1/Form_10_Square_EH14-EH19_LED_G3_0220.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/d24ce6955a4d461680d8ab7900e14a86/Form_10_Round_CA-MA_17-22_LED_G3_0220.pdf



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.