



	Best	Better	Better
	PureForm Post Top LED	Form Ten Round Post Top CPL	Form Ten Round Post Top MPL
Prefix	PPT	CPL	MPL
Lumen Output Range	2,000-9,000	5,037-21,852	5,037-21,852
Efficacy	82-104	93-113	93-113
Distribution	Type 1, 2, 3, 5	Type 2, 3, 4, 5	Type 2, 3, 4, 5
Color Temperature	2700, 3000, 4000, 5000, Amber	3000, 4000, 5700	3000, 4000, 5700
Mounting Height Range	10'-20'	10'-25'	10'-25'
0 Uplight	Yes	Yes	Yes
Auto Profile Dimming	Yes	No	No
Motion Response	Yes	No	No
SiteWise	Yes	No	No
Wireless Controls	Yes	No	No
Additional Luminaire Options	-	Comfort optics	Comfort optics
Mounting	T3, T2	-	-
Finish	Bronze, Black, White, Medium Grey, Dark Grey	Bronze Anodized, Black Anodized, Natural Anodized, Bronze, Black, White, Medium Grey	
IP Rating	IP66	-	-
Vibration	3G	-	-
DLC Listing	Standard	Standard	Standard
Certifications	UL/cUL	UL/cUL	UL/cUL
Lifetime	-	L70-100,000h	L70-100,000h
Limited Warranty	5 years		
Link	<a href="https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/293a281a6ad340779923aa4600b8a187/PPT_PureForm_post_top.pdf">https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/293a281a6ad340779923aa4600b8a187/PPT_PureForm_post_top.pdf</a>	<a href="https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/ba6f346a1efd4fdab1d4a87f01238b64/form_10_cp_mp_led.pdf">https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/ba6f346a1efd4fdab1d4a87f01238b64/form_10_cp_mp_led.pdf</a>	<a href="https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/ba6f346a1efd4fdab1d4a87f01238b64/form_10_cp_mp_led.pdf">https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/ba6f346a1efd4fdab1d4a87f01238b64/form_10_cp_mp_led.pdf</a>

