



	Best	Best	Better	Good
	PureForm Sconce Comfort	PureForm Sconce	121 LED	101 LED
Prefix	PWS	PWS	121	101
Lumen Output Range	2,200–9,700	4,900–21,800	2,600–9,370	2,747–9,800
Efficacy	92–111	94–137	76–114	81–110
Distribution	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4
Color Temperature	2700, 3000, 4000, 5000, Amber	2700, 3000, 4000, 5000, Amber	3000, 4000, 5700	3000, 4000, 5700
Mounting Height	8–20'	15–25'	8–20'	8–20'
0 Uplight	Yes	Yes	Yes	Yes
Emergency (0°C to 40°C)	Yes	Yes	Yes	Yes
Emergency Cold Pack (-20°C to 40°C)	Yes	Yes	Yes	Yes
Field Adjustable Wattage Selector (FAWS)	Yes	Yes	No	No
Dual Circuit Control (DCC)	No	Yes	Yes	Yes
Auto Profile Dimming	Yes	Yes	Yes	Yes
Motion Response	Yes	Yes	Yes	Yes
SiteWise	Yes	Yes	Yes	Yes
Wireless Controls	Yes	Yes	Yes	Yes
Photocell	Button	Button	Button	Button, TLRD5, TLRD7, TLRPC
Additional Options	Emergency Battery Backup	-	-	-
Finish	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey
IP Rating	IP65	IP66	IP66	IP66
DLC Listing	Standard	Premium	-	-
Certifications	UL/cUL	UL/cUL	Title 24	Title 24, cULus
Lifetime	L70–100,000h	L70–100,000h	L70–100,000h	L70–100,000h
Limited Warranty	5 years	5 years	5 years	5 years
Link	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/a5ae8afc40c34ccb-b268a88200895298/PWS_PureForm_wall_sconce_comfort.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/172eede6f00646b-fb8e8abb2007030f5/PWS_PureForm_wall_sconce_FWC.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/d955c55d6caa47b-fa26fab0400b22d24/121_LED_wall_sconce_G4.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/e737eb0948f24e7d-8e55a87f0121e910/101.pdf

Continued on next page.

Outdoor Wall Sconces



	Good	Good	Good	Good
	104 LED	102 LED	106 LED	107 LED
Prefix	104	102	106	107
Lumen Output Range	2,747-9,800	2,747-9,800	2,687-9,797	2,747-9,797
Efficacy	81-110	81-110	81-110	81-110
Distribution	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4
Color Temperature	3000, 4000, 5700	3000, 4000, 5700	3000, 4000, 5700	3000, 4000, 5700
Mounting Height	8-20'	8-20'	8-20'	8-20'
0 Uplight	Yes	Yes	Yes	Yes
Emergency (0°C to 40°C)	Yes	Yes	Yes	Yes
Emergency Cold Pack (-20°C to 40°C)	Yes	Yes	Yes	Yes
Field Adjustable Wattage Selector (FAWS)	No	No	No	No
Dual Circuit Control (DCC)	Yes	Yes	Yes	Yes
Auto Profile Dimming	Yes	Yes	Yes	Yes
Motion Response	Yes	Yes	Yes	Yes
SiteWise	No	No	No	No
Wireless Controls	Yes	Yes	Yes	Yes
Photocell	Button	Button	Button	Button
Additional Options	-	-	-	-
Finish	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey
IP Rating	IP66	IP66	IP66	IP66
DLC Listing	-	-	-	-
Certifications	Title 24, cULus	Title 24, cULus	Title 24, cULus	Title 24, cULus
Lifetime	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h
Limited Warranty	5 years	5 years	5 years	5 years
Link	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/332e9f4eb9a2466bab-c5a87f0121e510/104l.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/b58f3cfd5b4f479bb-1d9a87f01223642/102l.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/65e72c9a3a554e-04a22ea8820088bdec/106l.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/8ef40fa8aa3b-479283cca87f01223141/107l.pdf

Continued on next page.

Outdoor Wall Sconces



	Good	Good	Good
	111 Mini Sconce	161 LED	AeroScape LED Sconce
Prefix	111	161	ASW
Lumen Output Range	1,768-3,807	10,245-27,300	3,914-10,210
Efficacy	88-106	102-121	84-113
Distribution	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4
Color Temperature	3000, 4000, 5700	3000, 4000, 5700	3000, 4000, 5700
Mounting Height	-	-	-
0 Uplight	Yes	Yes	Yes
Emergency (0°C to 40°C)	-	No	No
Emergency Cold Pack (-20°C to 40°C)	-	No	No
Field Adjustable Wattage Selector (FAWS)	-	No	No
Dual Circuit Control (DCC)	-	Yes	No
Auto Profile Dimming	-	Yes	Yes
Motion Response	-	Yes	-
SiteWise	No	No	No
Wireless Controls	No	No	No
Photocell	Button	Button	Button
Additional Options	Diffusing lens	Custom color	-
Finish	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey
IP Rating	IP66	IP66	IP66
DLC Listing	-	-	-
Certifications	Title 24, cULus	cULus	cETLus
Lifetime	L70-100,000h	-	L70-100,000h
Limited Warranty	5 years	5 years	5 years
Link	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/edf20e34aef24d38bff0aa-5600c70a00/10-111_LED_Spec_Sheet_%281%29.pdf	https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/ef9d8522bfe247be-971da87f0123bf70/g_161_cut.pdf	-



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.