



	Best	Better	Better
	PureForm Post Top LED	Form Ten Round Post Top CPL	Form Ten Round Post Top MPL
Prefix	PPT	CPL	MPL
Lumen Output Range	2,000-9,000	5,037-21,852	5,037-21,852
Efficacy	82-104	93-113	93-113
Distribution	Type 1, 2, 3, 5	Type 2, 3, 4, 5	Type 2, 3, 4, 5
Color Temperature	2700, 3000, 4000, 5000, Amber	3000, 4000, 5700	3000, 4000, 5700
Mounting Height Range	10'-20'	10'-25'	10'-25'
0 Uplight	✓	✓	✓
Auto Profile Dimming	✓	-	-
Motion Response	✓	-	-
Wireless Controls	✓	-	-
Additional Luminaire Options	Emergency Battery Backup (cold weather and standard), Field Adjustable Wattage Selector (FAWS)	Retrofit Kit	Retrofit Kit
Mounting	T3, T2	Multiple tenon sizes to fit many pole sizes - see spec sheet for details	
Finish	Bronze, Black, White, Medium Grey, Dark Grey	Bronze Anodized, Black Anodized, Natural Anodized, Bronze, Black, White, Medium Grey	
IP Rating	IP66	Wet Location	Wet Location
Vibration	3G	-	-
DLC Listing	Standard	Standard	Standard
Certifications	UL/cUL	UL/cUL	UL/cUL
Lifetime	-	L70-100,000h	L70-100,000h
Limited Warranty	5 years		
Link			

